

## Myriad Adjustable Round - White with White bezel

MYRIAD ADJ ROUND WHITE 4000K PHDIM WHITE BEZ  
2056212



### Product features

- The Myriad Adjustable Round recessed spotlight is a high efficient accent downlight, fixture color RAL 9016 - Traffic white / Bezel, correlated colour temperature of 4000K, color rendering index Ra89, fixture lumen 702lm, total power consumption 10W, luminaire efficacy 70 lm/W, nominal light beam angle 24°, mains voltage 230-240V~ AC, control technology type: leading edge/trailing edge phase dim, product length 76mm, width 76mm, height 115mm, cut-out dimension 76mm, IP rating IP20, 5 years warranty.



### PRODUCT OVERVIEW

Product name	MYRIAD ADJ ROUND WHITE 4000K PHDIM WHITE BEZ
Technology	LED
Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
ETIM Class	EC001744
E-number FI	4278801
Warranty	5 years
Fixture luminous flux (lm)	702
Luminaire efficacy (lm/W)	70
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Beam Angle (°)	24
Photobiological Risk Group	RG1
Total power consumption (W)	10
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Housing colour	White
IP rating	IP20
IK rating	IK02
Product EAN number	5025768562121

### DATA TABLE

#### General data

Product name	MYRIAD ADJ ROUND WHITE 4000K PHDIM WHITE BEZ
Technology	LED

## Myriad Adjustable Round - White with White bezel

*MYRIAD ADJ ROUND WHITE 4000K PHDIM WHITE BEZ*  
2056212

Housing	PC Polycarbonate
Mount	Ceiling recessed mounting
Environment	Indoor
General application	Hospitality, Office, Residential & Consumer, Retail
Performance ambient temperature Tq (°C)	25
ETIM Class	EC001744
E-number FI	4278801
Warranty	5 years

### Optical data

Fixture luminous flux (lm)	702
Luminaire efficacy (lm/W)	70
LOR (%)	100
Colour temperature (K)	4000
Light colour	Neutral White
CRI (Ra)	90
Colour Variation Initial (SDCM)	SDCM3
Adjustable chromaticity	N
Beam Angle (°)	24
Distribution type	Symmetric
Photobiological Risk Group	RG1

### Electrical data

Total power consumption (W)	10
Mains voltage (V)	230-240V
Electrical protection	Class II
Control gear type	Electronic ballast
Control gear mounting	Integral
Transformer required	Yes
Drive current (mA)	250
Energy Efficiency Class (A->G) of contained light source	E
Nominal Frequency (Hz)	50/60Hz

### Lifetime data

Lifespan L70 B50	100000
Lifespan L80 B20	100000
Lifespan L90 B10	68500

### Physical data

Housing colour	White
IP rating	IP20
IK rating	IK02
Diffuser material	Glass
Nominal Product Width (mm)	76
Nominal Product Height (mm)	115
Cutout Dimensions (W x L in mm or Diameter in mm)	76
Max. Lamp Diameter (mm) - D	90

## Myriad Adjustable Round - White with White bezel

MYRIAD ADJ ROUND WHITE 4000K PHDIM WHITE BEZ  
2056212

Weight (kg)	0.38
Recessed Depth (mm)	115

### Packaging


Single packaging type	Carton
Product EAN number	5025768562121
Packaging single length / height (cm)	17.5
Packaging single width (cm)	15.0
Packaging single depth (cm)	17.5
DUN14 (outer)	05025768562121
Units per outer package	1
Packaging outer length / height (cm)	17.5
Packaging outer width (cm)	15.0
Packaging outer depth (cm)	17.5

## PHOTOMETRY

Distance [m]	Cone diameter [m]	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	1228 9701
0.5	0.23	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	3052 1425
1.0	0.46	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	1528 833
1.5	0.69	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	763 386
2.0	0.92	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	488 245
2.5	1.15	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	339 168
3.0	1.37	E <sub>0</sub> (°) E <sub>1</sub> (C0) E <sub>2</sub> (C2)	

Distance [m]      Cone diameter [m]      Illuminance [lx]

— C0 - C180 (Half beam angle: 25.5°)



## TECHNICAL DRAWINGS

