



Eaton 9PX 6000i RT3U Unterbrechungsfreie Stromversorgung (USV) Doppelwandler (Online) 6 kVA 5400 W 8 AC-Ausgänge

Marke : Eaton

Artikel-Code: 9PX6KIRTN-L

Produktname : 9PX 6000i RT3U



Eaton 9PX 6000i RT3U. USV-Topologie: Doppelwandler (Online), Ausgangskapazität: 6 kVA, Ausgangsleistung: 5400 W. AC-Steckertypen: C12-Koppler, C13-Koppler, Anzahl der AC-Ausgänge: 8 AC-Ausgänge. Akku-/Batterietechnologie: Lithium, Batteriekapazität: 6 Ah. Formfaktor: Rackmount/Tower, Produktfarbe: Schwarz, Silber, Rack-Kapazität: 3U



Merkmale		Merkmale	
USV-Topologie *	Doppelwandler (Online)	Effizienz	94%
Ausgangskapazität *	6 kVA	Anschlüsse und Schnittstellen	
Ausgangsleistung *	5400 W	AC-Steckertypen	C12-Koppler, C13-Koppler
Wellenform *	Sine	Anzahl der AC-Ausgänge	8 AC-Ausgänge
Eingangs-Betriebsspannung (min) *	176 V	Anzahl Ethernet-LAN-Anschlüsse (RJ-45)	1
Eingangs-Betriebsspannung (max) *	276 V	Akku/Batterie	
Eingangsfrequenz *	40/70 Hz	Akku-/Batterietechnologie	Lithium
Ausgangs-Betriebsspannung (min)	230 V	Batteriekapazität	6 Ah
Regulierung der Ausgangsspannung	1%	Anzahl Batteriezellen	15
Anzahl der Eingangs-Phasen	1	Hot-Swap-Batterie	✓
Anzahl der Ausgangs-Phasen	1	Design	
		Formfaktor *	Rackmount/Tower
		Rack-Kapazität	3U
		Produktfarbe *	Schwarz, Silber
		Display-Typ	LCD



0786689772604



786689772604

Disclaimer. The information published here (the "Information") is based on sources that can be considered reliable, typically the manufacturer, but this Information is provided "AS IS" and without guarantee of correctness or completeness. The Information is only indicative and can be changed at any time without notification. No rights can be based on the Information. Suppliers or aggregators of this Information do not accept any liability with regard to the content of (web)pages and other documents, including its Information. The publisher of the Information can not be held liable for the content of 3rd party websites that are linking this Information or are linked to from this Information. You as the User of the Information are solely responsible for the choice and usage of this Information. You are not entitled to transfer, copy or otherwise multiply or distribute the Information. You are obliged to follow the directions of the copyright owner(s) with regard to the use of the Information. Exclusively Dutch law is applicable. With regard to price and stock data on the site, the publisher followed a number of starting points, which are not necessarily relevant for your private or business circumstances. Therefore, the price and stock data are only indicative and are subject to changes. You are personally responsible for the way you use and apply this information. As a user of the Information or sites or documents in which this Information is included, you will adhere to standard fair use including avoidance of spamming, ripping, intellectual-property violations, privacy violations, and any other illegal activity.