



**Part no.: 50130445**  
**E4-V1-DS-B**  
**Signaling column element**



Figure can vary

## Contents

- Technical data
- Notes
- Accessories

Part no.: 50130445 – E4-V1-DS-B – Signaling column element

## Technical data

### Basic data

Series	E4
Suitable for	Signaling column elements of the E4 series
Type of signaling	Optical

### Electrical data

Life expectancy	> 100,000 h
-----------------	-------------

### Performance data

Supply voltage $U_B$	24 V , AC/DC , 10 %
Current consumption, max.	27 mA

### Mechanical data

Design	Cylindrical
Dimension ( $\varnothing$ x L)	40 mm x 62 mm
Housing material	Plastic
Net weight	45 g
Type of fastening	Bayonet system
Type of illuminant	LED/24V
Signal image	Continuous light
Lens color	Blue
Angle of radiation	360°

### Environmental data

Ambient temperature, operation	-30 ... 60 °C
--------------------------------	---------------

### Certifications

Degree of protection	IP 66
Certifications	c UL US

### Classification

Customs tariff number	85318070
eCl@ss 8.0	27371220
eCl@ss 9.0	27371220
ETIM 5.0	EC000232
ETIM 6.0	EC000232

## Notes

### Observe intended use!

- This product is not a safety sensor and is not intended as personnel protection.
- The product may only be put into operation by competent persons.
- Only use the product in accordance with its intended use.





## Part no.: 50130445 – E4-V1-DS-B – Signaling column element

### For UL applications:

- For UL applications, use is only permitted in Class 2 circuits in accordance with the NEC (National Electric Code).

## Accessories

### Mounting

	Part no.	Designation	Article	Description
	50130455	E4-MH1	Signaling column element	Connection: Terminal, Push-in technology Diameter: 40 mm Design: Horizontal mountingCylindrical Fastening, at system: Screw type / horizontal Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130458	E4-MP1-100	Signaling column element	Connection: Terminal, Push-in technology Diameter: 40 mm Design: Base mountingCylindrical Fastening, at system: Screw type / horizontal Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130456	E4-MW1	Signaling column element	Connection: Terminal, Push-in technology Diameter: 40 mm Design: Bracket mounting Fastening, at system: Screw type / vertical Lens modules: Max. 5 pieces Module holder: One side Ambient temperature: -30 ... 60 °C Degree of protection: IP 66
	50130457	E4-MW2	Signaling column element	Connection: Terminal, Push-in technology Diameter: 40 mm Design: Bracket mountingCylindrical Fastening, at system: Screw type / vertical Lens modules: Max. 10 pieces Module holder: Two-sided Ambient temperature: -30 ... 60 °C Degree of protection: IP 66

### Note

A list with all available accessories can be found on the Leuze electronic website in the Download tab of the article detailed page.