

MIRO 12.4 MULTI-TIMER

IN: 24 VAC/DC / 230 VAC - OUT: 230 VAC/DC / 6A


Relay output






Multitimer: 0.1...300


Spring clamp terminals

[Link to Product](#)

Illustration



Time	+A1	Function
0.1..1.2 s		Switch on delay
0.4..5 s		One shot
3.5..40 s		Modulation, pause starting
30..300 s		Modulation, pulse starting
		Switch off delay time



Product may differ from Image

Input

Input voltage	24 V AC/DC or 230 V AC ($\pm 15\%$)
Input current	12 mA (24 V DC)
Control voltage	24 V AC/DC...230 V AC ($\pm 15\%$)
Control current	2 mA

General data

Mech./ elect. life	20.000.000 switching cycles/load dependent
Test isolation voltage	4.8 kV
Mounting method	DIN-rail mountable (EN 60715)
Temperature range	-25...+60 °C

Output

Output voltage	max. 230 V AC/DC
Output current	max. 6 A
Min. load current	8 mA (24 V DC)
Output rating	max. 1500 VA/120 W
Contact material	Ag Sn O ₂
Energize/release/contact bounce time	8/10/2 ms

Commercial data

country of origin	CZ
customs tariff number	85364900
minimum order quantity	1