

AS-INTERFACE SHAPED CABLE "YELLOW, TPE, OIL-RESISTANT" SPECIAL DESIGN TO UL CLASS 2 2 X 1.5 QMM, 100M 1 PC. = 100 M



Figure similar

General technical data:		
Design of the product		AS-Interface shaped cables
Colour		yellow (AS-Interface)
Material		TPE special version according to UL Class 2
Quantity		100 m roll
Mechanical data:		
Without silicone precipitation		yes
bending radius according to DIN VDE 0298 Part 300		
• fixed min	m	12
• freely movable min	m	24
Without halogens		no
Flexibility		good
Bending behavior according according to DIN VDE 0472 Part 603		no break after 30000 reverse bending cycles
Core colours		brown, blue
Ambient conditions:		
Fire behavior		flame-retardant according to IEC 60332-1;VDE 0482 T. 265-2-1;UL 1581 sec. 1061 cable flame;UL 1685 CSA FT4
resistance to oil		resistant
Ozone and weather resistant		resistant
Temperature range		
• stationary	°C	-30 ... +90
• moved	°C	-20 ... +90

## Certificates/ approvals:

Approvals Canada	CSA		C22.2 No. 214-02
Approvals USA	UL		UL 758 AWM; UL 13 Class 2; UL 444 CMG
Monitored expertise (VDE)			no
General Product Approval	Shipping Approval	other	



[Environmental Confirmations](#)

[Declaration of Conformity](#)

## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

### Cax online generator

<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3RX90170AA00>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RX90170AA00/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

<http://www.automation.siemens.com/bilddb/index.aspx?attID9=3RX90170AA00&lang=en>

last modified:

09.03.2015