

## 30°, 45°, 60° chamfer cutters for milling inserts TCMT 1102.., TCMT 16T3..


**ATORN®**

### Application

Universal use for chamfering and deburring.

### Version

- with straight shank in accordance with DIN 1835 B
- Shaft tolerance h6
- Clamping screw tightening torque (indexable insert) M2.5 = 1.2 Nm, M4 = 5.2 Nm



<b>Art. No.</b>	<b>16107 332</b>
<b>Chamfer angle</b>	45 Degree
<b>Max. cutting edge diameter</b>	32.5 mm
<b>Min. cutting edge diameter</b>	10.4 mm
<b>Clearance length</b>	42 mm
<b>Length</b>	100 mm
<b>Shaft diameter</b>	25 mm
<b>Number of cutting edges</b>	2 PCS
<b>Suitable indexable insert no.</b>	2
<b>Suitable for indexable inserts</b>	TC.. 16T3..

### EAN-Code

4050293111699