


# RFNA4JGIE Datasheet

## Product Name // N Jack Straight 4 Hole Flange RF Connector

[View Product Page](#)



// Product Description:	
⊗ N Jack Straight 4 Hole Flange RF Connector	⊗ Dielectric withstanding Voltage: >1500V
⊗ Maximum Voltage: 500V	⊗ Impedance: 50Ohm
⊗ Temperature range: -55Â°C to +155Â°C	⊗ Body Material: Stainless Steel Passivation
⊗ Frecuency range: 0GHz - 18GHz	⊗ Contact Material: Beryllium Copper
⊗ VSWR:	

// General Information:	
Product Display Title:	N Type Series Socket 4 Hole Flange
Product Family:	Radio Frequency Connectors
Product Series:	N Type Series
Body Length:	19.00mm
Body Material:	Stainless Steel Passivation
Centre Contact Retention Force:	>26.7N
Contact Pin Material:	Beryllium Copper
Min Coupling Torque:	0.80Nm
Max Coupling Torque:	1.10Nm
Dielectric Withstanding Voltage:	>1500V
Durability:	>500 cycles
Flange Mount Length:	25.40mm
Function:	Female Flange Mount RF Connector
Impedance:	50Ohm
Insulation Resistance:	>5000MOhm
Insulator:	Adapter ASTM D 1710 & PEI
Max Operating Temperature:	+155°C
Min Operating Temperature:	-55°C
Mount Hole Distance:	18.30mm
Min Operating Frequency:	0GHz
Max Operating Frequency:	18GHz
Socket Diameter:	0.51mm
Thread Size:	5/8 24UNEF 2A
Voltage Max:	500V
Vswr:	<1.30

// Product PDF Links

[N Type Series Product Datasheet](#)