

3D Sensor

MLAS204

Part Number

ShapeDrive




- 10 Gbit/s interface for high speed data transfer
- 12 MP resolution
- Short recording times of up to 0.44 s

ShapeDrive MLAS 3D Sensors are distinguished by high precision for minimal measuring volumes. The ten models in this series are available in two performance classes with camera resolutions of 5 and 12 megapixels. All ShapeDrive sensors are ideally suited for use in industrial environments thanks to the rugged IP65 housing. With its 10 Gigabit Ethernet interface and five measuring ranges in each performance class, ShapeDrive is also distinguished by great diversity and high speed.


Technical Data

Optical Data	
Working range Z	270...470 mm
Measuring range Z	200 mm
Measuring range X	240 mm
Measuring range Y	160 mm
Resolution Z	10 μ m
Resolution X/Y	63 μ m
Camera Resolution	4096 x 3000 Pixel
Light Source	LED (blue)
Wavelength	460 nm
Service Life (T = +25 °C)	20000 h
Risk Group (EN 62471)	2
Max. Ambient Light	5000 Lux
Electrical Data	
Supply Voltage	18...30 V DC
Max. Current Consumption (U _b = 24 V)	3,5 A
Recording duration	0,44...2,15 s
Temperature Range	0...35 °C
Storage temperature	-5...70 °C
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Interface	Ethernet TCP/IP
Baud Rate	100 Mbit/s
Baud Rate (10 GbE)	10 Gbit/s
Protection Class	III
Mechanical Data	
Housing Material	Aluminium; Plastic
Degree of Protection	IP65
Connection	M12 x 1; 12-pin
Type of Connection Ethernet	M12 x 1; 8-pin, X-cod.
Optic Cover	Plastic
Weight	2500 g
Web server	yes
Connection Diagram No.	238 1022
Control Panel No.	A41
Suitable Connection Equipment No.	50 87
Suitable Mounting Technology No.	343







Ctrl. Panel



78 = Module status
85 = Link/Act LED



Legend

+	Supply Voltage +	nc	not connected	EN _A ES42Z	Encoder A/Ā (TTL)
-	Supply Voltage 0 V	U	Test Input	EN _B ES42Z	Encoder B/B̄ (TTL)
~	Supply Voltage (AC Voltage)	Ū	Test Input inverted	EN _A	Encoder A
A	Switching Output (NO)	W	Trigger Input	EN _B	Encoder B
Ā	Switching Output (NC)	W-	Ground for the Trigger Input	A _{MIN}	Digital output MIN
V	Contamination/Error Output (NO)	O	Analog Output	A _{MAX}	Digital output MAX
V̄	Contamination/Error Output (NC)	O-	Ground for the Analog Output	A _{OK}	Digital output OK
E	Input (analog or digital)	BZ	Block Discharge	SY _{IN}	Synchronization In
T	Teach Input	AWV	Valve Output	SY _{OUT}	Synchronization OUT
Z	Time Delay (activation)	a	Valve Control Output +	OL _T	Brightness output
S	Shielding	b	Valve Control Output 0 V	M	Maintenance reserved
RxD	Interface Receive Path	SY	Synchronization	rsv	reserved
TxD	Interface Send Path	SY-	Ground for the Synchronization	Wire Colors according to IEC 60757	
RDY	Ready	E+	Receiver-Line	BK	Black
GND	Ground	S+	Emitter-Line	BN	Brown
CL	Clock	±	Grounding	RD	Red
E/A	Output/Input programmable	S _n R	Switching Distance Reduction	OG	Orange
	IO-Link	Rx+/-	Ethernet Receive Path	YE	Yellow
PoE	Power over Ethernet	Tx+/-	Ethernet Send Path	GN	Green
IN	Safety Input	Bus	Interfaces-Bus A(+)/B(-)	BU	Blue
OSSD	Safety Output	L _a	Emitted Light disengageable	VT	Violet
Signal	Signal Output	Mag	Magnet activation	GY	Grey
Bi_D+/-	Ethernet Gigabit bidirect. data line (A-D)	RES	Input confirmation	WH	White
EN ₀ ES42Z	Encoder 0-pulse 0-0̄ (TTL)	EDM	Contactur Monitoring	PK	Pink
				GN _{YE}	Green/Yellow

Measuring Volume

