

# Fieldbus Gateway

## RS-232 to Fast Ethernet

# ZAG45FN01

Part Number



- Easy handling
- Gateway from RS-232/422/485 interfaces to Fast Ethernet

These fieldbus gateways allow an easy connection of sensors and scanners to Fast Ethernet.

Ethernet

### Technical Data

Electrical Data	
Supply Voltage	10...33 V DC
Current Consumption Gateway (U <sub>b</sub> = 24 V)	< 100 mA
Temperature Range	0...55 °C
Short Circuit Protection	yes
Reverse Polarity Protection	yes
Interface	
Interface	RS-232
Baud Rate RS-232	< 115200 Bd
Baud Rate Ethernet	< 100 MBd
Number of Bus Clients	512
Protection Class	III
Mechanical Data	
Material	Plastic PA
Weight	140 g
Degree of Protection	IP20
Connection Mode Supply Voltage	Terminal Block
Connection RS-Side	Terminal Block
Connection Bus Side	RJ45
DIN-Rail mounting	35 mm
Fast Ethernet	●
Connection Table No.	<b>43</b>
Suitable Connection Equipment No.	<b>74</b>

### Complementary Products

Software

