

## Surface Cleaner 250ml

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1 - Product identifier

Trade name/designation Surface Cleaner 250ml  
Chemical name  
Product-type Mixture  
Product code 1904 4125

#### 1.2 - Relevant identified uses of the substance or mixture and uses advised against

#### 1.3 - Details of the supplier of the safety data sheet

ECS Cleaning Solutions GmbH  
Wolfener Str. 32-34  
D-12681 Berlin Germany  
Telephone : +49 (0)30 / 36 46 40 36  
gunnar.kleinmann@ecsag.com

#### 1.4 - Emergency telephone number

Germany: Intoxications Information Center; +49 761 19240  
Switzerland: Swiss Toxicological Information Centre; +41 44 251 51 51  
Austria: Intoxication information center; +43 1 406 43 43

### SECTION 2: Hazards identification

#### 2.1 - Classification of the substance or mixture

Classification according to Regulation (EC) No 1272/2008 [CLP]

Not Classified	Not classified
----------------	----------------

#### 2.2 - Label elements

Labelling according to Regulation (EC) No. 1272/2008 [CLP]

Signal word : None  
Pictograms : None  
Hazard statements : None  
Precautionary statements

P101	If medical advice is needed, have product container or label at hand.
P102	Keep out of reach of children.
P103	Read carefully and follow all instructions.

#### EUH-phrases

EUH208	Contains citral (5392-40-5)   linalool; 3,7-dimethyl- 1,6-octadien-3-ol; dl-linalool; (78-70-6) . May produce an allergic reaction
--------	--

#### 2.3 - Other hazards

### SECTION 3: Composition / information on ingredients

#### 3.1 - Substances

Not applicable

## Surface Cleaner 250ml

### 3.2 - Mixtures

Chemical name	No	%	Class(es)	Specific concentration limit
water	CAS No. : 7732-18-5 Index No. : EC No. : 231-791-2	94.46		Not applicable
2-butoxyethanol, ethylene glycol monobutyl ether, butyl cellosolve	CAS No. : 111-76-2 Index No. : 603-014-00-0 EC No. : 203-905-0	< 5	Acute Tox. 4 Inhalation - H332 Acute Tox. 4 Oral - H302 Eye Irrit. 2 - H319 Skin Irrit. 2 - H315	ATE oral 1200
citral	CAS No. : 5392-40-5 Index No. : 605-019-00-3 EC No. : 226-394-6	< 0.8	Skin Irrit. 2 - H315 Skin Sens. 1 - H317	Not applicable
propan-2-ol, isopropyl alcohol, isopropanol	CAS No. : 67-63-0 Index No. : 603-117-00-0 EC No. : 200-661-7	< 0.5	Eye Irrit. 2 - H319 Flam. Liq. 2 - H225 STOT SE 3 (H336) - H336	Not applicable
linalool; 3,7-dimethyl- 1,6-octadien-3-ol; dl-linalool;	CAS No. : 78-70-6 Index No. : 603-235-00-2 EC No. : 201-134-4	< 0.5	Skin Sens. 1B - H317	Not applicable

## SECTION 4: First aid measures

### 4.1 - Description of first aid measures

<u>Following inhalation</u>	- No special measures are necessary. - Provide fresh air.
<u>Following skin contact</u>	- Wash immediately with: Water - When in doubt or if symptoms are observed, get medical advice.
<u>After eye contact</u>	- Rinse immediately carefully and thoroughly with eye-bath or water. - In case of eye irritation consult an ophthalmologist.
<u>After ingestion</u>	- Rinse mouth thoroughly with water. - Do NOT induce vomiting.

### 4.2 - Most important symptoms and effects, both acute and delayed

<u>Symptoms and effects - Following inhalation</u>	- No information available.
<u>Symptoms and effects - Following skin contact</u>	- No information available.
<u>Symptoms and effects - After eye contact</u>	- No information available.
<u>Symptoms and effects - After ingestion</u>	- No information available.

### 4.3 - Indication of any immediate medical attention and special treatment needed

## SECTION 5: Firefighting measures

### 5.1 - Extinguishing media

<u>Suitable extinguishing media</u>	- ABC-powder - Carbon dioxide (CO2) - Foam - Extinguishing powder
<u>Unsuitable extinguishing media</u>	- Full water jet

## Surface Cleaner 250ml

### 5.2 - Special hazards arising from the substance or mixture

Special hazards arising from the substance or mixture - No information available.

### 5.3 - Advice for firefighters

- Co-ordinate fire-fighting measures to the fire surroundings.

## SECTION 6: Accidental release measures

### 6.1 - Personal precautions, protective equipment and emergency procedures

For non-emergency personnel - Use personal protection equipment.  
- Provide adequate ventilation.

For emergency responders - No information available.

### 6.2 - Environmental precautions

- No information available.

### 6.3 - Methods and material for containment and cleaning up

Methods and material for containment - No information available.

Methods and material for cleaning up - Absorb with liquid-binding material (sand, diatomaceous earth, acid- or universal binding agents).  
- Wash with plenty of water.

Inappropriate techniques - No information available.

### 6.4 - Reference to other sections

- Disposal: see section 13  
- Personal protection equipment: see section 8

## SECTION 7: Handling and storage

### 7.1 - Precautions for safe handling

Recommendation - No special technical protective measures are necessary.

Advices on general occupational hygiene - No information available.

### 7.2 - Conditions for safe storage, including any incompatibilities

- No information available.

### 7.3 - Specific end use(s)

## SECTION 8: Exposure controls/personal protection

### 8.1 - Control parameters

2-butoxyethanol, ethylene glycol monobutyl ether, butyl cellosolve (111-76-2)	
IOELV TWA mg/m3 (UE)	98 mg/m3 Skin
IOELV TWA ppm (UE)	20 ppm Skin
IOELV STEL mg/m3 (UE)	246 mg/m3 Skin
IOELV STEL ppm (UE)	50 ppm Skin

## Surface Cleaner 250ml

propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)	
IOELV TWA mg/m3 (UE)	1250 mg/m3
IOELV TWA ppm (UE)	400 ppm
IOELV STEL mg/m3 (UE)	999 mg/m3
IOELV STEL ppm (UE)	400 ppm

### DNEL / PNEC

2-butoxyethanol, ethylene glycol monobutyl ether, butyl cellosolve (111-76-2)			
Type	Value	User	Effect
DNEL short-term oral (acute)	26.7 mg/kg	Consumers	Systemic
DNEL long-term oral (repeated)	6.3 mg/kg bw/day	Consumers	Systemic
DNEL acute inhalative	1091 mg/m3	Workers	Systemic
DNEL acute inhalative	246 mg/m3	Workers	Local
DNEL acute inhalative	426 mg/m3	Consumers	Systemic
DNEL acute inhalative	147 mg/m3	Consumers	Local
DNEL long-term inhalative	98 mg/m3	Workers	Systemic
DNEL long-term inhalative	59 mg/m3	Consumers	Systemic
PNEC aquatic, freshwater	8.8 mg/l		
PNEC aquatic, marine water	0.88 mg/l		
PNEC aquatic, intermittent release	26.4 mg/l		
PNEC sediment, freshwater	34.6 mg/kg		
PNEC sediment, marine water	3.46 mg/kg		
PNEC Secondary Poisoning	0.02 mg/kg		
PNEC sewage treatment plant (STP)	463 mg/l		

propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)			
Type	Value	User	Effect
DNEL long-term oral (repeated)	26 mg/kg bw/day	Consumers	Systemic
DNEL long-term inhalative	500 mg/m3	Workers	Systemic
DNEL long-term inhalative	89 mg/m3	Consumers	Systemic
DNEL long-term dermal	888 mg/kg bw/day	Workers	Systemic
DNEL long-term dermal	319 mg/kg bw/day	Consumers	Systemic
PNEC aquatic, freshwater	140.9 mg/l		
PNEC aquatic, marine water	140.9 mg/l		
PNEC aquatic, intermittent release	140.9 mg/l		
PNEC sediment, freshwater	552 mg/kg		
PNEC sediment, marine water	552 mg/kg		
PNEC Secondary Poisoning	160 mg/kg		
PNEC sewage treatment plant (STP)	2251 mg/l		

### 8.2 - Exposure controls

Appropriate engineering controls - No information available.  
Individual protection measures, such as personal protective equipment - Suitable protective clothing: lab coat



## SECTION 9: Physical and chemical properties

### 9.1 - Information on basic physical and chemical properties

Physical state                      Liquid                                      Appearance

## Surface Cleaner 250ml

<u>Colour</u>	colourless	<u>Odour</u>	characteristic
Odour threshold		No data available	
pH		8.4	
Melting point		No data available	
Freezing point		No data available	
Boiling point		No data available	
Flash point		> 61 °C	
Evaporation rate		No data available	
flammability		No data available	
Lower explosion limit		No data available	
Upper explosion limit		No data available	
Vapour pressure		No data available	
Vapour density		No data available	
Relative density		No data available	
Density		No data available	
Solubility (Water)		No data available	
Solubility (Ethanol)		No data available	
Solubility (Acetone)		No data available	
Solubility (Organic solvents)		No data available	
Log KOC		No data available	
Auto-ignition temperature		No data available	
Decomposition temperature		No data available	
Kinematic viscosity		No data available	
Dynamic viscosity		No data available	

### Particle characteristics

Particle size	No data available
---------------	-------------------

### 9.2 - Other information

VOC content	No data available
Minimum ignition energy	No data available
Conductivity	No data available

## **SECTION 10: Stability and reactivity**

### 10.1 - Reactivity

- This material is considered to be non-reactive under normal use conditions.

### 10.2 - Chemical stability

- The product is chemically stable under recommended conditions of storage, use and temperature.

### 10.3 - Possibility of hazardous reactions

- No hazardous reaction when handled and stored according to provisions.

### 10.4 - Conditions to avoid

- No information available.

## Surface Cleaner 250ml

### 10.5 - Incompatible materials

- No information available.

### 10.6 - Hazardous decomposition products

- Does not decompose when used for intended uses.

## SECTION 11: Toxicological information

### 11.1 - Information on hazard classes as defined in Regulation (EC) No 1272/2008

Acute toxicity - Not classified

#### Toxicity : Mixture

LD50 oral (rat)	No data available
LD50 dermal (rat)	No data available
LD50 dermal (rabbit)	No data available
LC50 inhalation (rat)	No data available
LC50 inhalation dusts and mists (rat)	No data available
LC50 inhalation vapours (rat)	No data available

- Based on available data, the classification criteria are not met.

#### Toxicity : Substances

2-butoxyethanol, ethylene glycol monobutyl ether, butyl cellosolve (111-76-2)	
LD50 oral (rat)	1400 mg/kg
LD50 dermal (rat)	> 2000 mg/kg
propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)	
LD50 oral (rat)	5840 mg/kg
LD50 dermal (rabbit)	13900 mg/kg
linalool; 3,7-dimethyl- 1,6-octadien-3-ol; dl-linalool; (78-70-6)	
LD50 oral (rat)	2790 mg/kg
LD50 dermal (rat)	5610 mg/kg
citral (5392-40-5)	
LD50 oral (rat)	6800 mg/kg
LD50 dermal (rat)	2000 mg/kg

Skin corrosion/irritation - Not classified

Serious eye damage/eye irritation - Not classified

Respiratory or skin sensitisation - Not classified

Germ cell mutagenicity - Not classified

Carcinogenicity - Not classified

Reproductive toxicity - Not classified

STOT-single exposure - Not classified

STOT-repeated exposure - Not classified

Aspiration hazard - Not classified

## Surface Cleaner 250ml

### 11.2 - Information on other hazards

## SECTION 12: Ecological information

### 12.1 - Toxicity

#### Toxicity : Mixture

EC50 48 hr crustacea	No data available
LC50 96 hr fish	No data available
ErC50 algae	No data available
ErC50 other aquatic plants	No data available
NOEC chronic fish	No data available
NOEC chronic crustacea	No data available
NOEC chronic algae	No data available
NOEC chronic other aquatic plants	No data available

#### Toxicity : Substances

2-butoxyethanol, ethylene glycol monobutyl ether, butyl cellosolve (111-76-2)	
LC50 96 hr fish	1464 mg/l
propan-2-ol, isopropyl alcohol, isopropanol (67-63-0)	
EC50 48 hr crustacea	9714 mg/l
LC50 96 hr fish	9640 mg/l
ErC50 algae	> 100 mg/l
linalool; 3,7-dimethyl- 1,6-octadien-3-ol; dl-linalool; (78-70-6)	
LC50 96 hr fish	27.8 mg/l
NOEC chronic algae	54.3 mg/l
citral (5392-40-5)	
EC50 48 hr crustacea	103.84 mg/l
LC50 96 hr fish	6.78 mg/l

- The substance/mixture does not fulfill the criteria of the acute aquatic toxicity according to Regulation (EC) No 1272/2008 [CLP], Annex I.

### 12.2 - Persistence and degradability

Biochemical oxygen demand (BOD)	No data available
Chemical oxygen demand (COD)	No data available
% of biodegradation in 28 days	No data available

- No information available.

### 12.3 - Bioaccumulative potential

Bioconcentration factor (BCF)	No data available
Log KOC	No data available

- No indication of bioaccumulation potential.

### 12.4 - Mobility in soil

- No information available.

### 12.5 - Results of PBT and vPvB assessment

---

## Surface Cleaner 250ml

---

12.6 - Endocrine disrupting properties

12.7 - Other adverse effects

- No information available.

---

### SECTION 13: Disposal considerations

---

13.1 - Waste treatment methods

Waste treatment methods - Dispose of waste according to applicable legislation.

Sewage disposal - No information available.

Special precautions for waste treatment - No information available.

Community or national or regional provisions - No information available.

---

### SECTION 14: Transport information

---

14.1 - UN number or ID number

Not applicable

14.2 - UN proper shipping name

Not applicable

14.3 - Transport hazard class(es)

Not applicable

14.4 - Packing group

Not applicable

14.5 - Environmental hazards

Not applicable

14.6 - Special precautions for user

Not applicable

14.7 - Maritime transport in bulk according to IMO instruments

Not applicable

---

### SECTION 15: Regulatory information

---

15.1 - Safety, health and environmental regulations/legislation specific for the substance or mixture

Substances REACH candidates None

Substances Annex XIV None

Substances Annex XVII None

VOC content No data available

15.2 - Chemical Safety Assessment

Chemical safety assessment carried out for the product - No information available.



## Surface Cleaner 250ml

### SECTION 16: Other information

#### SDS versions

Version	Issue date	Author	Description of the amendments
1	11/22/2022		

#### Texts of the regulatory sentences

Acute Tox. 4 Dermal	Acute toxicity (dermal) - Category 4
Acute Tox. 4 Inhalation	Acute toxicity (inhalative) - Category 4
Acute Tox. 4 Oral	Acute toxicity (oral) - Category 4
Eye Irrit. 2	Eye irritation - Category 2
Eye Irrit. 2A	Eye irritation - Category 2A
Flam. Liq. 2	Flammable liquid and vapour. - Category 2
H225	Highly flammable liquid and vapour
H302	Harmful if swallowed
H312	Harmful in contact with skin
H315	Causes skin irritation
H317	May cause an allergic skin reaction
H319	Causes serious eye irritation
H332	Harmful if inhaled
H336	May cause drowsiness or dizziness
Not Classified	Not classified
Skin Irrit. 2	Irritation, Category 2
Skin Sens. 1	Skin sensitization - Category 1
Skin Sens. 1B	Skin sensitization - Category 1B
STOT SE 3 (H336)	STOT-single exposure - Category 3 (H336)

\*\*\* \*\*