



Figure can vary

**Part no.: 50106960**  
**TKS 20x40.P**  
**Reflector**



## Contents

- Technical data
- Dimensioned drawings

Part no.: 50106960 – TKS 20x40.P – Reflector

## Technical data

<i>Basic data</i>	
Area of application	Pharmaceutical
<i>Mechanical data</i>	
Design	Rectangular
Mounting dimension, width	20 mm
Reflection surface width	16 mm
Mounting dimension, height	60 mm
Reflection surface height	38 mm
Mounting dimension, thickness	6 mm
Triple reflector size	2.3 mm
Reflector material	Plastic
Material of base material	Plastic
Chemical designation, reflector material	PES
Structure, active surface	Triple
Net weight	5 g
Type of fastening	Adhesive Through-hole mounting
Compatibility of materials	Alcohol ECOLAB H2O2
<i>Environmental data</i>	
Ambient temperature, operation	-40 ... 65 °C
<i>Certifications</i>	
Degree of protection	IP 67
<i>Classification</i>	
Customs tariff number	90029000
eCl@ss 8.0	27279203
eCl@ss 9.0	27273601
ETIM 5.0	EC002467
ETIM 6.0	EC002467

## Dimensioned drawings

All dimensions in millimeters

Part no.: 50106960 – TKS 20x40.P – Reflector

