

## T9 Circline Plus

FC32/865  
0001965

### Product features



### PRODUCT OVERVIEW

Product name	FC32/865
Technology	Fluorescent
Watt (Rated) (W)	32
Lamp shape	Ring
Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated
Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940727
E-number Norway	3845365
Luminous flux (lm)	2100
Colour temperature (K)	6500
Light colour	Daylight
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Photobiological Risk Group	Not applicable
Wattage (W)	32
Product Voltage (V)	84
Dimmable	Yes
Average life (Nominal) (h)	12000
Product EAN number	5410288019659

### DATA TABLE

#### General data

Product name	FC32/865
Technology	Fluorescent
Watt (Rated) (W)	32
Lamp shape	Ring
Type	T9 Circline Plus
Cap/Base	G10q
Lamp finish	Frosted/Coated

## T9 Circline Plus

FC32/865

0001965

Fixture rating	Enclosed
General application	Education, Hospitality, Logistics & Industry, Museums & Galleries, Office, Retail, Residential & Consumer
ETIM Class	EC000108
E-number FI	4940727
E-number Norway	3845365

### Optical data

Luminous flux (lm)	2100
Luminous flux (Rated) (lm)	2100
Ambient temperature for maximum luminous flux (°C)	25
Colour temperature (K)	6500
Light colour	Daylight
Colour Code	865
CRI (Ra)	80
Colour Variation Initial (SDCM)	SDCM5
Adjustable chromaticity	N
Photobiological Risk Group	Not applicable
Rated lumen maint. factor (%) at 4000 h 50Hz	78
Rated lumen maint. factor (%) at 6000 h 50Hz	77
Rated lumen maint. factor (%) at 8000 h 50Hz	76
Rated lumen maint. factor (%) at 12000 h 50Hz	74

### Electrical data

Wattage (W)	32
Watt (Rated) - High frequency (W)	32
Current (A)	0.45
Product Voltage (V)	84
Control gear required	Yes
Transformer required	No
Dimmable	Yes
Lamp Energy Label (class)	G
kWh per 1000 hours burning time	35

### Lifetime data

Average life (Nominal) (h)	12000
Average life (Rated) (h)	12000
Rated survival factor (%) at 2000 h 50Hz	99
Rated survival factor (%) at 4000 h 50Hz	97
Rated survival factor (%) at 6000 h 50Hz	92
Rated survival factor (%) at 8000 h 50Hz	85
Rated survival factor (%) at 12000 h 50Hz	50

### Physical data

Nominal Product Height (mm)	29
-----------------------------	----

## T9 Circline Plus

FC32/865

0001965

Nominal Product Diameter (mm)	299
Max. Length base to base (mm) - A	299
Length base to pin Min-Max (mm) - B	299
Max. Lamp Diameter (mm) - D	29
Weight (kg)	0.188


### Packaging

Single packaging type	Carton
Product EAN number	5410288019659
Packaging single length / height (cm)	30.53
Packaging single width (cm)	30.57
Packaging single depth (cm)	3.27
DUN14 (outer)	15410288019656
Units per outer package	12
Packaging outer length / height (cm)	43.3
Packaging outer width (cm)	32.4
Packaging outer depth (cm)	32.7


### Safety data

Lamp mercury content (mg)	3.5
Breakage cleaning instructions	Applicable
Special purpose lamp	No
Suitable for household illumination	Yes


## PHOTOMETRY



## TECHNICAL DRAWINGS



T9 Circline Plus  
FC32/865  
0001965



**32**  
kWh/1000h




T9 Circline Plus

FC32/865

0001965



0001965



**32**  
kWh/1000h



2019/2015