Enabling the Electronics Revolution



PSC-360 Hall-Effect End-of-Shaft Rotary Position Sensor



KEY FEATURES



True, contactless operation

Without any gears or mechanical interfaces the sensor is easily assembled and calibrated and subject to limited wear and tear over lifetime.



360 degree absolute position feedback

Endless mechanical rotational angle without dead band, keeps the position on power loss with programmable electrical angles from 15 to 360 degrees.



Made for harsh environments

The rugged package protects the sensor from dust, moisture, vibration and extreme temperatures for usage in the most demanding environments.



Durable and robust design

The non-contacting design allows for an extra-long product lifetime of up to 50 million cycles.



Integrated shaft

The magnet is securely fastened to the shaft and acts as only moving component in the sensor.



Adaptable to your requirements

Programmable transfer function and switch outputs as well as different output protocols and redundancy levels available.

DESCRIPTION

The robust PSC-360 is a cost-effective noncontacting rotary position sensor that provides high performance in harsh environments such as transportation, industrial and medical applications.

This compact sensor of Piher Sensing Systems is truly non-contacting with a permanent magnet that is securely fastened to the shaft and acts as the only moving component in the sensor. Redundant versions provide independent voltage outputs with fully customizable characteristics. Additionally a switch output can optionally be configured.

The endless rotation sensor is highly configurable with a programmable angular range between 15 and 360 degrees, different signal output options and support for low and high-voltage power supply. Sealed, flange mounted for easy positioning and with fly leads, it can be customized to fit any desired connector configuration.

Multi-turn configurations are available on request.

APPLICATIONS

Industrial

- Autonomous warehouse robotics
- ▶ Robotics and automation feedback
- ▶ Robot arm position
- ► Valve monitoring
- Conveyor operation

Transportation

- ► Steering wheel angle
- ▶ Pedal Position
- ► Suspension/height detection
- Fork height and mast tilt
- Bucket position
- ► Hitch position
- ► Transmission gear shift
- Marine
- ► Steering and shifter sensor

Home and Building Automation

HVAC systems



Hall-Effect End-of-Shaft Rotary Position Sensor

MECHANICAL SPECIFICATIONS			
	PSC-360	PSC-360U	
Rotational life	Up to 50.000.000 cycles		
Mechanical range	360° (endless rotation)		
Shaft diameter	6mm	6,35mm	

ELECTRICAL SPECIFICATIONS

		PSC-360	PSC-360U	
Linearity ¹		±1% absolute (±0.5% on request)		
Electrical angular ra	ange	Programmable from 15° to 360°		
Output protocols		Analog (Ratiometric), PWM Serial Protocol (SPI) upon request CAN SAE J1939 CAN OPEN	Analog (Ratiometric), PWM Serial Protocol (SPI)	
Output		Simple Redundant Full-redundant		
Switch output		On request	Configurable	
Resolution	CAN, Analog, PWM SPI	Up to 12 bit n/a	Up to 12 bit Up to 14 bit	
Supply voltage ²		5V ±10% 7V to 15V	5V ±10% 12V ±10% 15V ±10%	
Supply current	Single version Redundant version CAN version	n Typ 8.5 mA n Typ 17 mA n Typ 47 mA		
Voltage protection		±10V		
Self-diagnostic features		yes		
¹ Extremographic motorials close to the concert (i.e., shaft, mounting surface) may affect the concert's linearity				

¹ Ferromagnetic materials close to the sensor (i.e. shaft, mounting surface) may affect the sensor's linearity ²Voltages up to 25V possible on request.

ENVIRONMENTAL SPECIFICATIONS		
Operating and storage temperature ¹	-40° to +125°C	
Shock	50g	
Vibration	5-2000 Hz; 20g; Amax 0,75 mm	

¹Other specifications available

Hall-Effect End-of-Shaft Rotary Position Sensor



MOUNTING INSTRUCTIONS

- 1. Place the component on a flat surface.
- 2. Fit the actuator onto the shaft avoiding any mechanical play/wobble.
- 3. Fasten the two M4 screws (M4 washers are recommended).

CONNECTION SCHEME							
Color	Simple		Redundant		Full-redundant	CAN	SPI
	5V	7V to 15V	5V	7V to 15V			
Brown	Power supply	Power supply	Power supply	Power supply	Power supply 1	Power supply	Power supply
Blue	Ground	Ground	Ground	Ground	Ground 1	Ground	Ground
Black	Signal output	Signal output	Signal output 1	Signal output 1	Ground 2	CAN High	MOSI
White	n/a	n/a	Signal output 2	Signal output 2	Signal output 2	CAN Low	/SS
Red	n/a	n/a	n/a	n/a	Power supply 2	n/a	n/a
Yellow	n/a	n/a	n/a	n/a	Signal output 1	n/a	n/a
Grey	n/a	Not used	n/a	Not used	n/a	n/a	SCLK

More instructions of use on www.piher.net. Connector assembly available on request.

Amphenol Sensors

Hall-Effect End-of-Shaft Rotary Position Sensor





1 The analog output is ratiometric, proportional:

- for supply voltage "5V" to input voltage; - for supply voltage "RE" to 5V.

- Ior supply voltage RE to 3V.
 2 Other output functions available, please check availability. Enter CXXXX as long as the new output function is not defined.
 3 Models with ERA < 40° available on request
 4 Voltages up to 25V possible on request.
 5 Leave empty if not applicable. Default frequency is 200 Hz

OUTPUT FUNCTIONS ERA Redundant Standard Inverted CW C0001 360° C0000 C0002 90% 270° C0208 C0158 C0031 Output Level C0007 C0072 50% 180° C0036 120° C0024 C0032 10% standard inverted 90° C0011 C0025 ERA Mechanical Rotational Angle 270 → 45° 70° C0150 C0149 180 315° On request 180 → 90° 1800 270° 60° C0006 C0020 240° 120 → 120° 180° **090** → 135° 225° 180° 40° C0026 C0123 040 → 160° 180° 2000

Custom output functions on request.

PSC-360U Panel Mount Version



Amphenol Sensors

HOW TO ORDER - PANEL MOUNT VERSION (Example: PSC360U-F1A-C0000-ERA360-05E)



Hall-Effect End-of-Shaft Rotary Position Sensor

OUTPUT VOLTAGE DEPENDING ON MAGNET POSITION



Custom output functions on request.

CONTACT PIHER SENSING SYSTEMS FOR CUSTOM SOLUTIONS



Disclaimer:

Disclaimer:
The product information in this catalog is for reference purposes. Please consult for the most up to date and accurate design information.
Philer Sensors & Controls S.A., its affiliates, agents, and employees, and all persons acting on its or their behalf [collectively, "Piher"], disclaim any and all liability for any
errors, inaccuracies or incompleteness contained herein or in any other disclosure relating to any product described herein.
Pher disclaims any and all liability arising out of the use or application of any product described herein or of any information provided herein the maximum extent permitted
by law. The product specifications do not expand or otherwise modify Piher's terms and conditions of sale, including but not limited to the warranty expressed therein, which
apply to these products.
No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Piher:
The product shown herein are not designed for use in medical, life-saving, or life-sustaining application suless otherwise expressly indicated. Customers using or selling
Pher products not expressly indicated or use in such applications day on trick and agree to fully indemnify Philer for any damages arising or resulting from
such use or sale. Please contact authorized Piher personnel to obtain written terms and conditions regarding products designed for such applications.
Product names and markings noted herein may be trademarks of their respective owners. Information contained in and/or attached to this datage use ay be subject to export
control regulations of the European Community. USA, or other countries. Each recipient of this document cortaricitated to this catalogue may be subject to export
control regulations of the European Community. USA, or other countries. Each recipient of this document cortaricitated to this dataget or tourder regulations. If you are in any dubt about the export that usage and/or transfer of any information
contained i



Vial T2, N°22 31500 Tudela Spain

sales@piher.net

Europe:	+34 948 820 450
Americas:	+1 636 251 0855
Asia Pacific:	+65 9641 8886
India:	+91 9538 686 586

