

Offset clamp, with adjustable support screw, complete



Application:

For clamping workpieces.

Version:

- With support screw and clamping screw
- Made from heat-treated steel
- Painted



Art. no.	26222 040
For table grooves according to DIN 650	16 mm
Suitable screw DIN 787	M16 x 125 mm
Min./max. clamping range	36-71 mm
Groove width	18 mm
Span iron length	160 mm
Span iron width	50 mm
Thread dimension	M16
Thread length	55 mm
Thickness	25 mm
Distance	51.5 mm
Length	50 mm

EAN-Code

402077207 130 1