

grinding and control vices, type PL-S MICRO

Operated with hexagon socket key



Application:

For horizontal, vertical and lateral grinding, inspection and eroding tasks.

Execution:

- Made of alloyed tool steel.
- Hardened and precision-ground.
- Quick adjustment.
- Perpendicularity tolerance 0.005 mm/100 mm (base area to fixed jaw clamping surfaces).
- Ref. no. 110-150, parallelism tolerance 0.002 mm/100 mm (base area to upper guide plate).
- Ref. no. 110-120: type PL-S MICRO, ref. no. 130-150: type PL-S.



Art. no.	28600 130
Brand	RÖHM
Manufacturer Part Number	1179516
Model	Type PL-S with quick adjustment
Prism countersunk horizontally and vertically	Yes
Jaws width	70 mm
Jaws height	30 mm
Height 2	32 mm
Clamping width	80 mm
Height	62 mm
Body length	160 mm
Length 2	33 mm
Length 3	45 mm
Gross Weight	3.260 kg
Product Group	202

EAN

4019208228242