

3-point internal measuring probe set with dial gauge Marator 1086 R

Micromar 844 A



Application:

For measuring through-bores and blind bores and short centring shoulders in series production.

Execution:

- Self-centring and self-aligning
- Carbide-tipped measuring faces
- Interchangeable measuring heads

Delivery:

1 measuring element, measuring heads with setting rings, operating instructions, Marator 1086 R dial gauge



Art. no.	31913 610
Brand	MAHR
Manufacturer Part Number	4487760
Min./max. length measuring range	6-12 mm
Error limit	3 µm
Data transmission type	USB
Digit increment	0.0005 mm
Model	844 AS
IP protection class	IP 42
Number of measurement heads	3 PCS
Adjusting ring diameter	8 mm, 10 mm
Preset function	Yes
With ABS function	Yes
Number of rechargeable batteries/batteries	1 PCS
Battery designation	3V CR2032 Lithium
Included in delivery	MarCator 1086 R, operating instructions, adjusting rings. Key for changing measuring heads (from 30 mm), hexagon key, case
Gross Weight	2.058 kg
Product Group	305

EAN

4059192021610