

## LD40 diamond cutting disc – ideal for flexible applications in soft to hard materials

Segment height 12.0 mm

# RHODIUS

### Application:

For cutting reinforced concrete, stone and similar materials. Suitable for wet and dry sanding

### Version:

- Laser-welded
- Segmented
- Reducing rings for bore diameters 20.0 mm and 22.2 mm are included with each 300 mm and 350 mm disc

|                                    |                  |
|------------------------------------|------------------|
| <b>Art. no.</b>                    | <b>76119 230</b> |
| <b>Washer diameter</b>             | 230 mm           |
| <b>Washer thickness</b>            | 2.4 mm           |
| <b>Bore diameter</b>               | 22.23 mm         |
| <b>Max. rotation speed</b>         | 6650 rpm         |
| <b>Form</b>                        | Straight         |
| <b>Number of pieces per packet</b> | 1 PCS            |
| <b>Material to be processed</b>    | Stone, Concrete  |



### EAN-Code

4011890050347