

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023
Version: 7.0
Replaces version: 6.0
Language: en-GB
Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 1 of 7

SECTION 1: Identification of the substance/mixture and of the company/undertaking

1.1 Product identifier

Trade name: Aqua 90

This safety data sheet pertains to the following products:

LZB 120: 5 L

LZB 220: 10 L

LZB 320: 20 L

UFI: JA20-U0DT-H001-PA3W

1.2 Relevant identified uses of the substance or mixture and uses advised against

General use: Heat transfer fluids
Industrial use
Professional uses / Public domain

1.3 Details of the supplier of the safety data sheet

Company name: Lauda Dr. R. Wobser GmbH & Co. KG
Street/POB-No.: Laudaplatz 1
Postal Code, city: DE-97922 Lauda-Königshofen
WWW: www.lauda.de
E-mail: info@lauda.de
Telephone: +49 (0)9343-503-0
Telefax: +49 (0)9343-503-222
Department responsible for information:
Department Quality Management,
Telephone: +49 9343 503-331, e-mail info@lauda.de

1.4 Emergency telephone number

National Poisons Information Service (Birmingham Unit)
Telephone: 844 892 0111

SECTION 2: Hazards identification

2.1 Classification of the substance or mixture

Classification according to EC regulation 1272/2008 (CLP)

This mixture is classified as not hazardous.

2.2 Label elements

Labelling (CLP)

Hazard statements: not applicable

Precautionary statements: not applicable

2.3 Other hazards

No risks worthy of mention.

Endocrine disrupting properties, Results of PBT and vPvB assessment:
No data available

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023
Version: 7.0
Replaces version: 6.0
Language: en-GB
Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 2 of 7

SECTION 3: Composition/information on ingredients

3.1 Substances: not applicable

3.2 Mixtures

Chemical characterisation: Aqueous solution of organic bacteriostatic and fungistatic compounds

Additional information: The product does not contain dangerous substances above limits that need to be mentioned in this section according to applicable legislation.

SECTION 4: First aid measures

4.1 Description of first aid measures

In case of inhalation: Provide fresh air.

Following skin contact: Remove residues with soap and water. Change contaminated clothing. In case of skin reactions, consult a physician.

After eye contact: Immediately flush eyes with plenty of flowing water for 10 to 15 minutes holding eyelids apart. Remove contact lenses, if present and easy to do. Continue rinsing. In case of eye irritation consult an ophthalmologist.

After swallowing: Rinse mouth. Seek medical treatment in case of troubles.

4.2 Most important symptoms and effects, both acute and delayed

After eye contact: May cause irritations.

4.3 Indication of any immediate medical attention and special treatment needed

Treat symptomatically.

SECTION 5: Firefighting measures

5.1 Extinguishing media

Suitable extinguishing media: The product itself does not burn. Extinguishing is to be in accordance with the surrounding fire.

Extinguishing media which must not be used for safety reasons:

Full water jet

5.2 Special hazards arising from the substance or mixture

Hazardous vapours may form during fires.

5.3 Advice for firefighters

Special protective equipment for firefighters:

Wear self-contained breathing apparatus.

Additional information:

Hazchem-Code: -

Contaminated fire-fighting water must be collected separately.

Do not allow water used to extinguish fire to enter drains, ground or waterways.

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023

Version: 7.0

Replaces version: 6.0

Language: en-GB

Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 3 of 7

SECTION 6: Accidental release measures

6.1 Personal precautions, protective equipment and emergency procedures

Wear appropriate protective equipment. Keep unprotected people away.
Provide adequate ventilation. Do not breathe vapour/aerosol.

6.2 Environmental precautions

Do not allow to enter into ground-water, surface water or drains.

6.3 Methods and material for containment and cleaning up

Soak up with absorbent materials such as sand, siliceous earth, acid- or universal binder. Store in special closed containers and dispose of according to ordinance.

6.4 Reference to other sections

Refer additionally to section 8 and 13.

SECTION 7: Handling and storage

7.1 Precautions for safe handling

Advices on safe handling: Provide adequate ventilation, and local exhaust as needed.
Do not breathe vapour/aerosol.
Avoid contact with skin and eyes.
When using do not eat, drink or smoke. Wear appropriate protective equipment.

Precautions against fire and explosion:
No special measures are required.

7.2 Conditions for safe storage, including any incompatibilities

Requirements for storerooms and containers:
Keep container tightly closed. Store at room temperature.

Hints on joint storage: Keep away from food, drink and animal feedingstuffs.

7.3 Specific end use(s)

No information available.

SECTION 8: Exposure controls/personal protection

8.1 Control parameters

Additional information: Contains no substances with occupational exposure limit values.

8.2 Exposure controls

Vapours/aerosols should be exhausted directly at the point of origin.

Personal protection equipment

Occupational exposure controls

Respiratory protection: Use a breathing protection against vapours/aerosol.
Use filter type A-P2 according to EN 14387.

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023
 Version: 7.0
 Replaces version: 6.0
 Language: en-GB
 Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 4 of 7

Hand protection: Protective gloves according to EN 374.
 Glove material:
 Natural latex - Layer thickness 0.6 mm, Breakthrough time: 60 min
 Nitrile rubber - Layer thickness 0.4 mm, Breakthrough time: 480 min
 Observe glove manufacturer's instructions concerning penetrability and breakthrough time.

Eye protection: Tightly sealed goggles according to EN 166.

General protection and hygiene measures:
 Do not breathe vapour/aerosol. Avoid contact with skin and eyes.
 Change contaminated clothing.
 When using do not eat, drink or smoke.
 Wash hands before breaks and after work.

Environmental exposure controls

Refer to "6.2 Environmental precautions".

SECTION 9: Physical and chemical properties

9.1 Information on basic physical and chemical properties

Appearance:	Physical state at 20 °C and 101.3 kPa: liquid Colour: blue, clear
Odour:	weak
Odour threshold:	No data available
pH:	No data available
Melting point/freezing point:	0 °C
Initial boiling point and boiling range:	100 °C
Flash point/flash point range:	No data available
Evaporation rate:	No data available
Flammability:	No data available
Explosion limits:	No data available
Vapour pressure:	at 20 °C: 23 hPa
Vapour density:	No data available
Density:	at 20 °C: 0.95 - 1.05 g/mL
Water solubility:	completely miscible
Partition coefficient: n-octanol/water:	No data available
Auto-ignition temperature:	not self-igniting
Decomposition temperature:	heating: > 150 °C
Viscosity, kinematic:	No data available
Explosive properties:	Product is not explosive.
Oxidizing characteristics:	No data available

9.2 Other information

Solvent content:	0 %
Water content:	>= 99 %

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023

Version: 7.0

Replaces version: 6.0

Language: en-GB

Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 5 of 7

SECTION 10: Stability and reactivity

10.1 Reactivity

refer to 10.3

10.2 Chemical stability

Stable under recommended storage conditions.

10.3 Possibility of hazardous reactions

No dangerous reactions are known.

10.4 Conditions to avoid

heating: > 95 °C

10.5 Incompatible materials

No data available

10.6 Hazardous decomposition products

No hazardous decomposition products when regulations for storage and handling are observed.

Thermal decomposition: heating: > 150 °C

SECTION 11: Toxicological information

11.1 Information on toxicological effects

Toxicological effects:

The statements are derived from the properties of the single components. No toxicological data is available for the product as such.

Acute toxicity (oral): Based on available data, the classification criteria are not met.

Acute toxicity (dermal): Based on available data, the classification criteria are not met.

Acute toxicity (inhalative): Based on available data, the classification criteria are not met.

Skin corrosion/irritation: Based on available data, the classification criteria are not met.

Serious eye damage/irritation: Based on available data, the classification criteria are not met.

Sensitisation to the respiratory tract: Based on available data, the classification criteria are not met.

Skin sensitisation: Based on available data, the classification criteria are not met.

Germ cell mutagenicity/Genotoxicity: Based on available data, the classification criteria are not met.

Carcinogenicity: Based on available data, the classification criteria are not met.

Reproductive toxicity: Based on available data, the classification criteria are not met.

Effects on or via lactation: Lack of data.

Specific target organ toxicity (single exposure): Based on available data, the classification criteria are not met.

Specific target organ toxicity (repeated exposure): Based on available data, the classification criteria are not met.

Aspiration hazard: Based on available data, the classification criteria are not met.

Symptoms

After eye contact: May cause irritations.

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023

Version: 7.0

Replaces version: 6.0

Language: en-GB

Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 6 of 7

SECTION 12: Ecological information

12.1 Toxicity

Further details: No data available

12.2 Persistence and degradability

Further details: No data available

12.3 Bioaccumulative potential

Partition coefficient: n-octanol/water:

No data available

12.4 Mobility in soil

No data available

12.5 Results of PBT and vPvB assessment

No data available

12.6 Other adverse effects

General information: Do not allow to enter into ground-water, surface water or drains.

SECTION 13: Disposal considerations

13.1 Waste treatment methods

Product

Recommendation: Dispose of waste according to applicable legislation.
Do not dispose of with household waste. Do not empty into drains.

Package

Waste key number: 15 01 02 = Plastic packaging
Recommendation: Dispose of waste according to applicable legislation.
Non-contaminated packages may be recycled.

SECTION 14: Transport information

14.1 UN number

ADR/RID, IMDG, IATA-DGR: not applicable

14.2 UN proper shipping name

ADR/RID, IMDG, IATA-DGR: Not restricted

14.3 Transport hazard class(es)

ADR/RID, IMDG, IATA-DGR: not applicable

14.4 Packing group

ADR/RID, IMDG, IATA-DGR: not applicable

SAFETY DATA SHEET

according to Regulation (EC) No 1907/2006, as retained and amended in UK law [UK REACH]

Revision date: 9/1/2023

Version: 7.0

Replaces version: 6.0

Language: en-GB

Date of print: 20/3/2023

Aqua 90

Material number LZB x20

Page: 7 of 7

14.5 Environmental hazards

Marine pollutant: NO

14.6 Special precautions for user

No dangerous good in sense of these transport regulations.

14.7 Transport in bulk according to Annex II of Marpol and the IBC Code

No data available

SECTION 15: Regulatory information

15.1 Safety, health and environmental regulations/legislation specific for the substance or mixture

National regulations - Great Britain

Hazchem-Code:

-

No data available

15.2 Chemical Safety Assessment

For this mixture a chemical safety assessment is not required.

SECTION 16: Other information

Further information

Abbreviations and acronyms:

- ADN: European Agreement concerning the International Carriage of Dangerous Goods by Inland Waterways
- ADR: European Agreement concerning the International Carriage of Dangerous Goods by Road
- AS/NZS: Australian Standards/New Zealand Standards
- CAS: Chemical Abstracts Service
- CFR: Code of Federal Regulations
- CLP: Classification, Labelling and Packaging
- DMEL: Derived minimal effect level
- DNEL: Derived no-effect level
- EC: European Community
- EN: European Standard
- EQ: Excepted quantities
- IATA: International Air Transport Association
- IATA-DGR: International Air Transport Association – Dangerous Goods Regulations
- IBC Code: International Code for the Construction and Equipment of Ships carrying Dangerous Chemicals in Bulk
- IMDG Code: International Maritime Dangerous Goods Code
- MARPOL: Maritime Pollution: The International Convention for the Prevention of Pollution from Ships
- OSHA: Occupational Safety and Health Administration
- PBT: Persistent, bioaccumulative and toxic
- PNEC: Predicted no-effect concentration
- RID: Regulations Concerning the International Carriage of Dangerous Goods by Rail
- TRGS: Technical Rules for Hazardous Substances
- TSCA: Toxic Substance Control Act
- vPvB: Very persistent and very bioaccumulative

Reason of change: General revision

Date of first version: 13/9/2012

Department issuing data sheet

Contact person: see section 1: Department responsible for information

The information in this data sheet has been established to our best knowledge and was up-to-date at time of revision. It does not represent a guarantee for the properties of the product described in terms of the legal warranty regulations.