



Figure similar

COOLING UNIT DOOR OR WALL MOUNTED COOLING CAPACITY 1050 W 230 V AC RAL 7035 400X950X233 MM (WXHxD) INTERBAL CYCLE IP 54 OUTSIDE CYCLE IP 34

Model		
product brand name		SIVACON
Product designation		Cooling device
Design of the control cabinet cooler		Air/air
General technical data		
A-rated sound power level / maximum	dB	65
Operating pressure / maximum permissible	bar	25
Cooling capacity / at L35L35	W	1 050
<b>Temperature</b>		
• of the inner cooling circuit / minimum	°C	20
• of the inner cooling circuit / maximum	°C	46
• of the outer cooling circuit / minimum	°C	20
Electricity		
Starting current	A	10.5
Main circuit		
<b>Operating voltage</b>		
• with AC / at 50 Hz / Rated value / maximum	V	230
• with AC / at 60 Hz / Rated value / maximum	V	230
<b>Operating current</b>		
• of the fuse link / Rated value	A	6
• for motor / maximum rated value	A	3.1
Product details		
Product component		

- Heating
- Thermostat

No  
Yes

## Connections

Type of electrical connection Connector, 4-pole

## Mechanical Design

Height	mm	950
Width	mm	400
Depth	mm	233
Installation location		Mounting, parti... integration
Material		steel

## Certificates

### Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

E  
E

## General Product Approval



## Further information

### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

### Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8MR64235SK10>

### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8MR64235SK10/all>

### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

[http://www.automation.siemens.com/bilddb/cax\\_en.aspx?mfb=8MR64235SK10](http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=8MR64235SK10)

### CAX-Online-Generator

<http://www.siemens.com/cax>

### Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>

last modified:

11.03.2015