


## Customer Information Sheet

DRAWING No.: M80-FCXXXFI-XX-XXXXL IF IN DOUBT - ASK NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm







I. CABLE ASSEMBLIES ARE PACKED IN BAGS OF 10.

2. FOR COMPLETE SPECIFICATION SEE COMPONENT SPECIFICATION COO5XX AND CO49XX (LATEST ISSUES).

DIMENSION	MEASUREMENT
DIM 'A'	(4 x No. OF CONTACTS) - 4.00
DIM 'B'	(4 x No. OF CONTACTS) + 5.00
DIM 'C'	(4 x No. OF CONTACTS) + 10.0
EXAMPLE PART No.:	
2 CONTACT CONNECTOR WITH 300mm OF 10AWG WIRE =	

M80-FCPF5F1-02-0300L 12 CONTACT CONNECTOR WITH 150mm OF 12AWG WIRE = M80-FC325F1-12-0150L

## ORDER CODE: M80-FCXXXFI-XX-XXXXL

POWER CONTACT:-305 = COAX CONTACT CRIMP RG178 M80-305 325 = POWER CONTACT SOLDER 12AWG M80-325 326 = POWER CONTACT SOLDER 14AWG M80-326 327 = POWER CONTACT SOLDER 16AWG M80-327 328 = POWER CONTACT CRIMP 18AWG M80-328 329 = POWER CONTACT CRIMP 20AWG M80-329 PF5 = POWER CONTACT SOLDER 10AWG M80-PF5

TOTAL No. OF CONTACTS: 02 TO 12

0150 = 150 mm0300 = 300 mm0450 = 450mm

26.04.19 21886 DATE APPROVED: R. PORTLOCK CHECKED: S.BENNETT DRAWN: F.MCGOWAN CUSTOMER REF.:

ASSEMBLY DRG:

www.harwin.com technical@harwin.com THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES MATERIAL: X. = ±1mm X.X = ±0.50mm

 $X.XX = \pm 0.20$ mm  $X.XXX = \pm 0.01$ mm FINISH: SEE ABOVE ANGLES = ±5° S/AREA: UNLESS STATED

SEE ABOVE

-DIM 'D' LENGTH:

0060 = 60 mm MIN

9999 = 9999mm MAX

(SEE TABLE FOR EXAMPLES)

-STOCKED CABLE LENGTHS:

TITLE: DATAMATE POWER FEMALE SINGLE-ENDED CABLE ASSEMBLY WITH JACKSCREW

DRAWING NUMBER:

M80-FCXXXFI-XX-XXXXL

OF,