

## SSDC clamping holder, positive neutral

For longitudinal turning with SC indexable insert

**ATORN**<sup>®</sup>

### Application

For longitudinal turning with SC indexable insert, 45°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

### Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



<b>Art. no.</b>	<b>17849 150</b>
<b>ISO name</b>	SSDC N 1212 F09
<b>Shaft height</b>	12 mm
<b>Shank width</b>	12 mm
<b>Length</b>	80 mm
<b>Length of head</b>	16 mm
<b>Programming size</b>	6 mm
<b>Suitable for indexable inserts</b>	SC.. 09T3..
<b>Tool design</b>	Neutral

### EAN-Code

4050293563238