

PDUN steel boring bar, negative, right

for copy and longitudinal turning using DN indexable insert

ATORN[®]

Application


For copy turning and longitudinal turning using DN 55° indexable insert

Version

- precision-manufactured steel boring bar, D type, 93° pitch angle, 55° tip angle, 0° clearance angle

Advantage

- very slim geometry, optimised for contour turning work
- negative body geometry ensures good stability and absorption of force for large cutting depths



Art. No.	17853 001
ISO name	S 20 S PDUN R/L 11
Min. bore diameter	25 mm
Shaft diameter	20 mm
Clearance length	29 mm
Length	250 mm
Clamping surface height	18 mm
Programming size	13 mm
Cutting edge height	9 mm
Suitable for indexable inserts	DN.. 1104..
Tool design	Right
DIN	8024

EAN-Code

4050293 126990