

Micrometer

Narrow measuring surfaces

Mitutoyo

Application:

For measuring narrow external recesses.

Execution:

- Semi-gloss chrome-plated scale drum and sleeve
- Carbide-tipped measuring faces or hardened blades
- Friction coupling for consistent, repeatable measuring force
- Non-rotating measuring spindle

Advantage:

- Accesses hard-to-reach measuring points

Delivery:

Includes box, adjustment wrench



Art. no.	32116 562
Brand	MITUTOYO
Manufacturer Part Number	122-162-10
Min./max. length measuring range	25-50 mm
Vernier scale	0.01 mm
Measuring spindle increments	0.5 mm
Bracket depth	49 mm
Spindle clamping	No
Error limit	3 µm
Display	Nonius
Min./max. measurement force	3-8 N
Calibration Group	D
Gross Weight	0.315 kg
Product Group	3MA

EAN

4946368847542