

Drawer cabinet system 800 S with 11 drawers


Depth 800 mm, width 722 mm

Execution:

- Load capacity of 70 kg with a drawer front height of 60 mm and 100 kg with a drawer front height of 90 mm
- Solidly welded steel sheet construction
- Tilt-proof due to built-in individual drawer pull-out locking
- The drawers have high-quality Delrin rollers which means that they run quietly
- Drawers with slots all around for inserting compartment rails and dividers
- Drawers with perforated steel sheet base (25 mm hole spacing) for attaching and fixing individual items
- Aluminium grip handles with paper and cellophane strips and lateral cover caps
- Load capacity of 100 kg with a drawer front height of 90 mm

Advantage:

- Optimum operating characteristics of drawers
- High quality - made in Germany



Art. no.	50310 121
Brand	HK
Manufacturer Part Number	50310121
Number of drawers	11 PCS
Height	1568 mm
Width	722 mm
Depth	800 mm
Height x width x depth	1568 x 722 x 800 mm
Drawer width (inner dimension) x drawer depth (inner dimension)	600 x 700 mm
Drawer with slots	Yes
Perforated drawer base	Yes
Load-carrying capacity per drawer	200 kg
Drawer surface	0.42 m ²
Pullout type	Full extension
With SOFT-CLOSE closing function	No
With single pull-out safety brake	Yes
Central locking	Yes
Material of cover panel	Wood, plastic-coated
Cabinet colour	Light grey RAL 7035
Colour of front	Anthracite grey RAL 7016
Surface	Powder-coated
Functions	RFID possible
Model	S8 49/11
Overall surface	4.62 m ²
Lock type	DOM® locking system
Material	Sheet steel
Gross Weight	252.000 kg
Product Group	5BB

EAN

4053625404933