

swivel hoist ring, quality class 10

Screwed attachment point with ball bearing

CARTEC

Application:

Screw-on, rotating attachment point for lifting heavy loads that need to be rotated or turned. Suitable for safe lifting in accordance with Machinery Directive 2006/42/EC.

Execution:

- quality class 10 - compact, lightweight design, with DGUV certification
- with ball bearing for easier loading, loadable in all directions
- Can be rotated through 360°, swivel range of bracket max. 180°
- salmon, powder-coated surface
- permanent rotation under full load not permitted

Advantage:

- 4-way safety in every load direction
- constructed, tested and certified according to GS-OA 15-04 - EN 1677



Art. no.	77236 125
Brand	CARTEC
Manufacturer Part Number	C800X0402430
Thread dimension	M24
Load-carrying capacity	4 t
Internal width	40 mm
Bracket diameter	18 mm
Interior height	70 mm
Width of support plate	58 mm
Distance between lower edge of retainer holder and screw head	68 mm
Distance between lower edge of retainer holder and retainer	153 mm
Usable thread length	30 mm
Width across flats	48 mm
Gross Weight	1.543 kg
Product Group	775

EAN

8013429800726