


VARTA's Lithium assortment fulfills the highest quality and performance demands in all areas of modern life. The perfect solution for energy-intensive fields of application like digital cameras, GPS systems and smoke detectors, Lithium batteries also work exceptionally well under extreme conditions. VARTA Lithium batteries master temperature ranges from -40 degrees Celsius up to +60 degrees Celsius. High-tech devices are supplied with maximum performance and endurance. Up to 38% reduced weight in comparison to alkaline: perfect for sport and outdoor usages. In addition, VARTA's Lithium technology allows a guaranteed storage time of 15 years (except 9V).





PORTABLE POWER

PROFESSIONAL/BUTTON CELLS



Indoors or outdoors - professional solutions for ultimate needs

VARTA Lithium batteries are available in different sizes so that the maximum performance can be reached for every kind of application.

Available as:

Туре	Voltage (V)	System	Width (mm)	Height (mm)	Depth (mm)	Diameter (mm)	Weight (g)	IEC	Others
6103	1.5	Lithium	-	44.5	-	10.5	7.7	FR10G445	Micro, AAA
6106	1.5	Lithium	-	50.5	-	14.5	14.5	FR14505	Mignon, AA
6122	9.0	Lithium	26.5	49.2	17.5	-	36.4	-	9V, E-Block

For more details, see page 94

LITHIUM

















	-5 x MONE FORMS	- 5 x MODE FORMS	S anima strains	SX must be west	And in case of the last	
Туре	e 6103		6106	6106	6122	
Others	hers AAA, Micro		AA, Mignon	AA, Mignon	9V, E-Block	
Order-No./ consumer unit	06103 301 402	06103 301 404	06106 301 402	06106 301 404	06122 301 401	
Batteries/ consumer unit	2	4	2	4	1	
Width (mm) Blister	80	80	80	80	80	
Height (mm) Blister	120	120	120	120	120	
Depth (mm) Blister	12	12	16	16	19	
Weight (g) Blister	20	35	33	62	41	
Minimum pieces/shipment unit	10	10	10	10	10	
Innercarton	10	10	10	10	10	
Mastercarton	50	50	100	100	50	
Voltage (V)	1.5	1.5	1.5	1.5	9.0	
Electrochemical System	Lithium	Lithium	Lithium	Lithium	Lithium	
Width (mm) Battery	-	-	-	-	26.5	
Height (mm) Battery	44.5	44.5	50.5	50.5	49.2	
Depth (mm) Battery	-	-	-	-	17.5	
Diameter (mm) Battery	10.5	10.5	14.5	14.5	_	
Weight (g) Battery	7.7	7.7	14.5	14.5	36.4	
EC FR10G445		FR10G445	FR14505	FR14505	_	
Details	tails Page 10		Page 10	Page 10	Page 10	
EAN/GTIN/ consumer unit	7 008496 880399	4 008496 680436	724089 964800 4	4 008496 680511	4 100849611675265	

^{*} UL certified. Underwrites Laboratories www.ul.com