

We measure it. **testo**



## Digital Vacuum Gauge with Bluetooth®

**testo 552** - For evacuating  
refrigeration/air conditioning  
systems and heat pumps

---

Highly accurate and reliable measurement results

---

Measurement data monitoring via testo Smart Probes App

---

Measurement data dispatch via testo Smart Probes App

---

Measurement of the evaporation temperature of H<sub>2</sub>O

---

Optical alarm when a limit value is exceeded

---

Extremely robust and water/dirt resistant (IP 42)

---



mbar

micron



Bluetooth  
+ App

testo Smart Probes App  
for free download



testo 552 is a digital vacuum gauge for the evacuation of refrigeration systems and heat pumps. It measures even the smallest absolute pressures, and delivers highly accurate information about a system's status of dehumidification (removal of foreign matter, incl. oils, foreign gases, etc.).

Via a Bluetooth interface, the testo 552 connects with the testo Smart Probes App on your smartphone or tablet. This allows you to monitor the absolute pressure reached during the evacuation conveniently and wirelessly. In addition to this, the measurement results can be quickly documented in the App and sent by e-mail.

Its robust construction makes it ideal for everyday use, protected against dirt and water.


[www.testo.com](http://www.testo.com)

# Technical data/accessories

**testo 552**

testo 552, digital vacuum gauge with Bluetooth connection for wireless monitoring of measurement results

Order no. 0560 5522

**testo Smart Probes App**

The App turns your smartphone/tablet into the display of the testo 552. The operation of the measuring instrument as well as the display of the measurement values take place by Bluetooth via the Smart Probes App on your smartphone or tablet – independently of the measurement location. In addition to this, you can use the App to create measurement reports, add photos and comments, and send them by e-mail. For iOS and Android.

| Accessories   | Order no. |
|---|-----------|
| Connection cable with MiniDin plug for connecting testo 552 to the digital manifold testo 570 | 0554 5520 |

| Sensor type                          | Absolute pressure sensor  |
|--------------------------------------|---|
| Vacuum measuring range               | 0 to +26.66 mbar / 0 to 20 000 microns  |
| Accuracy vacuum ±1 digit (at +22 °C) | ±10 microns + 10 % of m.v. (100 to 1 000 microns)   |
| Vacuum resolution                    | 1 micron (0 to 1 000 microns)<br>10 microns (1 000 to 2 000 microns)<br>100 microns (2 000 to 5 000 microns)<br>500 microns (5 000 to 10 000 microns)<br>5 000 microns (10 000 to 20 000 microns) |
| Overload vacuum                      | absolute: 6 bar / 87 psi<br>relative: 5 bar / 72 psi  |

| General technical data       |   |
|------------------------------|---|
| Storage temperature          | -20 to +50 °C   |
| Operating temperature        | -10 to +50 °C   |
| Dimensions                   | 250 x 165 x 55 mm   |
| Weight                       | Approx. 500 g   |
| Protection class             | IP42  |
| Battery type                 | 2 AA batteries  |
| Battery life                 | 50 hrs (without Bluetooth/backlighting)   |
| Connection                   | 2 x 1/4" SAE (7/16" UNF)<br>1 x mini - DIN (connection to testo 570)                              |
| Measurement value sensor     | Pirani sensor   |
| Parameters                   | mmHg, Torr, mbar, hPa, micron, inH <sub>2</sub> O, inHg, Pa                                       |
| Measurement rate             | 0.5 s   |
| Warranty                     | 2 years   |
| Compatibility App connection | requires iOS 8.3 or newer / Android 4.3 or newer<br>requires mobile end device with Bluetooth 4.0 |

1981 0844/msp/l/03.2016

Subject to change, including technical modifications, without notice.

