



ANNEX

EU TYPE EXAMINATION CERTIFICATE Nr. 049/2023/0690

1. Applicant

Kroschke sign-international GmbH
Kroschkestrasse 1
38112 Braunschweig
Germany

2. Description

EN 388:2016+A1:2018



4 1 3 1 A

3. Materials and accessories

Gloves

- SecuLight®, art. nr. 12876 -12880



4. Technical documentation

Summary test results

EN ISO 21420:2020

Gloves

SecuLight®, art. nr. 12876 -12880

Method	Description	Result	Class
ISO 3071:2020	pH - textile	PASS	
ISO 14362-1:2017	AZO dyes for colored gloves	PASS	
ISO 16190:2021	Polycyclic aromatic hydrocarbons (PAHs)	PASS	
EN 16778:2016	Dimethylformamide (DMFa)	PASS	
EN ISO 21420:2021 §6.1	Length	PASS	
1149-1 / 1149-3 or EN 16350	Electrostatic properties	/	/
EN ISO 21420:2020 §6.2	Dexterity	/	/
ISO 11092:2014 textile	Water vapour transmission	/	/

EN 388:2016+A1:2018

Gloves

SecuLight®, art. nr. 12876 -12880

Method	Description	Result	Class
EN 13594:2015 §6.9	Impact Test	/	/
EN 388 6.1	Abrasion resistance	PASS	Level 4
EN 388 6.2	Cut resistance	PASS	Level 1
EN 388 6.4	Tear resistance	PASS	Level 3
EN 388 6.5	Puncture resistance	PASS	Level 1
ISO 13997 6.3	Cut resistance	PASS	Level A

Description/Picture of article

Article **The Gloves SecuLight®**
art. nr. 12876 (size 7) · 12877 (size 8) · 12878 (size 9) · 12879 (size 10) · 12880 (size 11)



The above picture is a general picture of the article. Possible variations of the above article can be present in the technical file.

Note :

Any modification in material, design, or other technical features must be brought to the attention of the Notified Body.