

CONTACTOR SIZE 2, 2-POLE DC-3 AND 5, 32 A AUX.
SWITCHES 22 (2NO+2NC) DC OPERATION 800 V DC
0.7...1.2 US

General technical data:

Size of contactor		2
Number of poles		2
Equipment marking acc. to DIN 40719 extended according to IEC 204-2 acc. to IEC 750		K
Equipment marking acc. to DIN EN 61346-2		Q
Protection class IP		IP00
Ambient temperature during operation	°C	-25 ... +55

Control circuit/ Control:

Type of voltage		DC
Control supply voltage		800 ... 800
• for DC Rated value	V	

Main circuit:

Number of NO contacts for main contacts		2
Number of NC contacts for main contacts		0
Operating current		
• at DC-3 at DC-5		
— at 440 V Rated value	A	29
— at 220 V Rated value	A	32
— at 600 V Rated value	A	21
— at 750 V Rated value	A	7.5
Operating power		
• at DC-3 at DC-5		
— at 110 V Rated value	kW	2.5

— at 220 V Rated value	kW	5
— at 440 V Rated value	kW	9
— at 600 V Rated value	kW	9
— at 750 V Rated value	kW	4

Auxiliary circuit:

Identification number and letter for switching elements		22
Number of NO contacts for auxiliary contacts		2
Number of NC contacts for auxiliary contacts		2
Number of CO contacts for auxiliary contacts		0

Connections/ Terminals:


Type of electrical connection for main current circuit		screw-type terminals
Type of electrical connection for auxiliary and control current circuit		screw-type terminals

Mechanical data:

Mounting type		screw and snap-on mounting onto 35 mm standard mounting rail according to DIN EN 50022
Mounting type Side-by-side mounting		Yes
Width	mm	70
Height	mm	85
Depth	mm	145

Certificates/ approvals:

General Product Approval	Functional Safety/Safety of Machinery	Test Certificates
 CCC	 CSA	 UL
		
	Type Examination Certificate	Special Test Certificate

Shipping Approval	other
 RMRS	other Declaration of Conformity

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)
<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)
<http://www.siemens.com/industrymall>

last modified:

09.03.2015