

Revolving centring point

With impact absorption



Application:

For fine turning, rough machining and copying on lathes.

Execution:

- Tip angle 60°.
- Bearings supported on a spring pack for impact absorption.
- Body and moving point are hardened and ground.
- Moving point can be reground multiple times.
- For absorbing impact loads and compensating for linear expansion.

Advantage:

- Special seal prevents the ingress of dirt and coolant.
- Precision roller bearings ensure a high level of concentricity.
- Maintenance-free owing to permanent lubrication.

Delivery:

1x revolving centring point.



Art. no.	22126 050
Brand	RÖHM
Manufacturer Part Number	42843
Morse taper size	MK 5
Programming size	129 mm
Programming size for housing	78.5 mm
Max. workpiece weight	2000 kg
Max. rotation speed	3000 rpm
Concentricity tolerance	0.005 mm
Diameter of housing	90 mm
Tip diameter	40 mm
Gross Weight	4.521 kg
Product Group	201

EAN

4019208014364