

Short-length chucks

ERICKSON system with straight shank

ORION[®]

Application:

For use on NC and CNC machining equipment.

Execution:

- Min. tensile strength at core 800 N/mm.
- Hardened.
- Clamping of drill bits on drill heel possible.
- With adjustable longitudinal stop.
- Collets no. 23326.

Advantage:

- With straight shank - extremely slim version.
- Very good accessibility in confined spaces.

Delivery:

1x ERICKSON short chuck system with cylindrical shank.



| | |
|---------------------------------|------------------|
| Art. no. | 23325 295 |
| Brand | ORION |
| Manufacturer Part Number | 23325295 |
| Collet type | DKS |
| Shank diameter | 8 mm |
| Min./max. clamping width | 1-4 mm |
| Width across flats | 9 mm |
| Outer diameter | 10 mm |
| Shaft length | 100 mm |
| Length of head | 32 mm |
| Min. clamp in depth | 20 mm |
| Max. clamp in depth | 42 mm |
| Gross Weight | 0.083 kg |
| Product Group | 218 |

EAN

4039247 156962