



- NOTES: FINISH (PLATING THICKNESS IN MICRO-INCHES)
1. BRASS PER QQ-B-626
  2. BRASS PER QQ-B-613
  3. GOLD PL. 3 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  4. BERYLLIUM COPPER PER QQ-C-530
  5. GOLD PL. 30 MIN. THICK OVER NICKEL PL. 100 MIN. THICK OVER COPPER STRIKE
  6. TEFLON MIL-P-19468
  7. ZINC DIECAST

1. CRIMPED FERRULE  
HEX CRIMP SIZE .128"  
2. CONTACT PIN TO SOLDER

DIMENSIONS ARE IN MILLIMETERS			
UNLESS OTHERWISE SPECIFIED TOLERANCES			
0.5-6	= ±0.2		
6-30	= ±0.4		
30-120	= ±0.6		
120-315	= ±1		
315-1000	= ±1.6		
1000-2000	= ±2.4		

PART NO.	SMB6112D1-3GT30G-5-50
APPROVED	DATE 10-11-01'
CHECKED	DATE 10-11-01'
DRAWN	DATE 10-11-01'
FILE NO	

<b>Amphenol</b>	
TITLE SMB R/A CRIMP PLUG (FOR RG-174/U,188A/U,316/U)	
DRAWING NO. KJ-SMB6112D1-3GT30G-316U-50	
ITEM NO.	

8	HEAT SHRINK TUBING			1	HT-56/5X193
7	COVER	NOTE 2	NOTE 3	1	CV-523X06-T
6	FERRULE	COPPER	NOTE 3	1	FR-38/3X7C
5	CONTACT PIN	NOTE 4	NOTE 5	1	SMB5091-5-B
4	INSULATOR	NOTE 6	NATURAL	1	SMB5003-3T-50
3	RETAINER RING	NOTE 4	NATURAL	1	SMB5000-6
2	BODY	NOTE 1	NOTE 3	1	SMB6112D1-2-C
1	HOUSING	NOTE 7	NOTE 3	1	SMB6112D1-1-23/17
NO.	DESCRIPTION	MATERIAL	FINISH	Q'TY	DRAWING NO.