

3-point internal micrometer

IMICRO



Application:

For high-precision measurement of through-bores, even at high measuring depths.

Execution:

- Measuring faces made of hardened steel
- Friction coupling for consistent, repeatable measuring force
- Self-centring and self-aligning

Advantage:

- Ground step taper for high precision
- Insensitive to influence of body heat from the user's hand and fluctuations in ambient temperature
- The only 3-point internal micrometer working on the Abbe principle

Delivery:

In cardboard box



Art. no.	31695 017
Brand	TESA
Manufacturer Part Number	00810802
Min./max. length measuring range	14-17 mm
Measuring depth	77 mm
Error limit	4 µm
Vernier scale	0.005 mm
Measuring spindle increments	0.5 mm
Calibration Group	I
DIN	863
Calibration Group Description	Internal micrometers (3 point)
Gross Weight	0.610 kg
Product Group	362

EAN

7630041108095