

Pneumatic straight grinder SRH 8-30/2

With lever valve



Application:

For fine finishing, smoothing and deburring.

Execution:

- Environmentally friendly owing to central air discharge
- Air discharge to the rear

Delivery:

Collet chuck ZG 7/6mm, collet chuck key SW 11 + 14



Art. no.	75036 075
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150010925
Model	SRH 8-30/2
Valve design	Lever valve
Max. idle speed	30000 rpm
Power output	240 W
Air consumption	450 l/min
Connection thread	R 1/8 inch
Inner hose diameter	7 mm
Length	189 mm
Diameter of housing	31 mm
Max. clamping diameter	8 mm
Suitable for max. sanding block diameter	16 mm
Max. HM rotating milling cutter diameter	10 mm
Weight	0.41 kg
Gross Weight	1.089 kg
Product Group	748