

## Rotary drive units ERMS

**FESTO**



This product is also available as a modular mechanical system  
Rotary drive ERMO



## Key features

### At a glance Plug and work with the Simplified Motion Series



The simplicity of pneumatics is now combined for the first time with the advantages of electric automation thanks to the Simplified Motion Series. These integrated drives are the perfect solution for all users who are looking for an electric alternative for very simple movement and positioning tasks between two mechanical end positions, but don't want the commissioning process for traditional electric drive systems that can often be quite complex.


Integrated	Simple	Standardised	Connected
<p>The integrated electronics in the drive are at the core of the Simplified Motion Series.</p>	<p>For commissioning, simply set all relevant parameters directly on the drive:</p> <ul style="list-style-type: none"> <li>• Speed and force</li> <li>• Reference end position and cushioning</li> <li>• Manual operation</li> </ul>	<p>Electrical connection via M12 plug design</p> <ul style="list-style-type: none"> <li>• Power (4-pin): power supply for the motor</li> <li>• Logic (8-pin): control signal, sensor signal and power for the integrated electronics</li> </ul>	<p>Use of extended functions possible via IO-Link:</p> <ul style="list-style-type: none"> <li>• Motion parameters can be set remotely</li> <li>• Copy and backup function for transferring parameters</li> <li>• Read function for extended process parameters</li> </ul>

## IO-Link

There is no need for any software since operation is simply based on the "plug and work" principle. Digital I/O (DIO) and IO-Link are always automatically included – a product with two types of control as standard.


### The functions of the Simplified Motion Series

Basic profile for movement between two end positions: with speed control










- These drives are designed for simple movements between two end positions.
- Proximity sensors are required in order to implement any intermediate positions.

Extended motion profile for simplified press-fitting and clamping functions: with speed and force control



### The products in the Simplified Motion Series

<p>Spindle axis unit ELGS-BS-KF</p> 	<p>Toothed belt axis unit ELGS-TB-KF</p> 	<p>Mini slide unit EGSS-BS-KF</p> 	<p>Electric cylinder unit EPCS</p> 
<p>Toothed belt axis unit ELGE</p> 	<p>Rotary drive unit ERMS</p> 	<p>Electric cylinder unit EPCE</p> 	

## Key features

### At a glance



- Without external servo drive: all the necessary electronic components are combined in the integrated drive
- Two control options integrated as standard: digital I/O and IO-Link
- Complete solution for simple movements between mechanical end positions
- Simplified commissioning: all parameters can be manually set directly on the drive
- No special expertise required for commissioning
- End-position feedback similar to that of a conventional proximity sensor is integrated as standard
- Sealed hollow shaft for the integrated through-feed of cables and tubing
- Standardised mounting interface for direct connection to the electric mini slides EGSL, EGSC and EGSS

### Modular and flexible with motor, motor mounting kit and servo drive

This product is also available within the Optimised Motion Series as rotary drive ERMO:





Rotary drive and motor in one unit. Compact and powerful rotating and swivelling with no limits. Sturdy and precise owing to backlash-free ball bearing.

- Rotary drive in 4 sizes for torque of up to 5 Nm
- Hollow shaft for energy through-feed for attachments
- Optional pneumatic or electric energy chain
- Optional proximity sensor for homing or position sensing
- Optional holding brake
- Modular: individual combinations with servo drive

### Key features



**Possible combinations with Festo drives**

Rotary drive unit ERMS on electric cylinder EPCO





Size		Accessories	
[1] ERMS	[2] EPCO	Centring sleeve	Screw
25	40	ZBH-7 (x2)	M5x20 (x2)

Rotary drive unit ERMS on mini slide unit EGSS




Size		Accessories	
[1] ERMS	[2] EGSS	Centring sleeve	Screw
25	45, 60	ZBH-7 (x2)	M5x12 (x2)
32	60	ZBH-7 (x2)	M5x15 (x2)

Rotary drive unit ERMS on mini slide EGSL




Size		Accessories	
[1] ERMS	[2] EGSL	Centring sleeve	Screw
25	55	ZBH-7 (x2)	M5x14 (x2)
32	55	ZBH-7 (x2)	M5x14 (x2)

Rotary drive unit ERMS on mini slide DGSL



The proximity sensor SIEN cannot be used as a reference sensor on the ERMO when ERMO-12 is combined with DGSL-12.



Size		Accessories	
[1] ERMS	[2] DGSL	Centring sleeve	Screw
25	20	ZBH-9-7 (x2)	M5x22 (x2)
25	25	ZBH-9-7 (x2)	M5x22 (x2)

## Type codes

001	Series	
ERMS	Rotary drive	

002	Size	
25	25	
32	32	

003	Nominal swivel angle	
90	90°	
180	180°	

004	Motor type	
ST	Stepper motor ST	

005	Controller	
M	Integrated	

006	Control panel	
H1	Integrated	

007	Bus protocol/activation	
PLK	PNP and IO-Link®	
NLK	NPN and IO-Link®	


008	End-position sensing	
AA	With integrated end-position sensing	

009	Cable outlet direction	
	Standard	
L	Left	
R	Right	

010	Electrical accessories	
	None	
L1	Adapter for operation as IO-Link® device	

011	Operating instructions	
	With operating instructions	
DN	No operating instructions	

Peripherals overview




Motor mounting variants


Standard

[L] Left

[R] Right



Control elements





[1] Pushbutton actuators for parameterisation and control

## Peripherals overview

Accessories		
Type/order code	Description	→ Page/Internet
[1] IO-Link master USB CDSU-1	For straightforward use of the mini slide unit via IO-Link	21
[2] Adapter NEFC-M12G8	Connection between the motor and the IO-Link master	21
[3] Connecting cable NEBC-M12	For connection to a controller	20
[4] Supply cable NEBL-T12	For connecting load and logic supply	20
[5] Centring sleeve ZBH	<ul style="list-style-type: none"> <li>• For centring attachments</li> <li>• For centring the rotary drive</li> </ul>	20
[6] Adapter kit DHAA	For drive/gripper connections	adapter kit

## Data sheet

-  Size  
25, 32
-  Rotation angle  
90°, 180°



General technical data			
Size		25	32
Design		Electromechanical rotary drive with integrated drive	
Rotation angle		90, 180	
Gear ratio		9:1	7:1
Mounting position		Optional	
Additional functions		Integrated end-position sensing User interface	
Display		LED	
Homing		Positive fixed stop block Negative fixed stop block	
Type of mounting		Via female thread	
Max. cable length			
Inputs/outputs	[m]	15	
IO-Link operation	[m]	20	
Product weight		1472	2304

Mechanical data			
Size		25	32
Permissible mass moment of inertia	[kgcm <sup>2</sup> ]	65	164
Peak torque	[Nm]	2.7	5.6
Max. speed	[rpm]	150	100
Max. speed at 90°	[rpm]	105	100
Speed press	[rpm]	3	2
Angular acceleration	[rad/s <sup>2</sup> ]	≤140	
Repetition accuracy	[°]	±0.05	±0.1
Torsional backlash <sup>1)</sup>	[°]	0.2	0.2

1) Without load in new condition



## Data sheet

<b>Electrical data</b>			
Size		25	32
<b>Motor</b>			
Nominal voltage DC	[V]	24 (±15%)	
Nominal current	[A]	3	5.3
Max. current consumption (load)	[A]	3	5.3
Max. current consumption (logic)	[mA]	300	
<b>Encoder</b>			
Rotor position encoder		Absolute encoder, single turn	
Rotor position encoder measuring principle		Magnetic	
Rotor position encoder resolution	[bit]	16	
<b>Interfaces</b>			
Size		25	32
<b>Parameterisation interface</b>			
IO-Link		Yes	
User interface		Yes	
<b>Digital inputs</b>			
Quantity		2	
Switching logic		PNP	
		NPN	
Characteristics		Not galvanically isolated	
		Configurable	
Specification		Based on IEC 61131-2, type 1	
Operating range	[V]	24	
<b>Digital outputs</b>			
Quantity		2	
Switching logic		PNP	
		NPN	
Rotor position encoder		Absolute encoder, single turn	
Characteristics		Not galvanically isolated	
		Configurable	
Max. current	[mA]	100	


## Data sheet

Technical data – IO-Link		
Size	25	32
SIO mode support	Yes	
Communication mode	COM3 (230.4 kBd)	
Connection technology	Plug	
Port class	A	
Number of ports	1	
Process data width OUT	[byte]	2
Process data content OUT	[bit]	1 (Move in)
	[bit]	1 (Move out)
	[bit]	1 (Quit Error)
Process data width IN	[byte]	2
Process data content IN	[bit]	1 (State Device)
	[bit]	1 (State Move)
	[bit]	1 (State in)
	[bit]	1 (State out)
Service data content IN	[bit]	32 (Force)
	[bit]	32 (Position)
	[bit]	32 (Speed)
Minimum cycle time	[ms]	1
Data memory required	[kilobyte]	0.5
Protocol version	Device V 1.1	
Operating and environmental conditions		
Size	25	32
Insulation class	B	
Ambient temperature	[°C]	0 ... +50
Storage temperature	[°C]	-20 ... +60
Note on ambient temperature	Above an ambient temperature of 30°C, the power must be reduced by 2% per K	
Temperature monitoring	Switch-off for excessive temperature	
	Integrated precise CMOS temperature sensor with analogue output	
Relative humidity	[%]	0 ... 85
Protection class	III	
Degree of protection	IP40	
Duty cycle	[%]	100
CE marking	To EU EMC Directive	
	To EU RoHS Directive	
KC mark	KC EMC	
Certification	RCM compliance mark	
Vibration resistance	Transport application test with severity level 1 to FN 942017-4 and EN 61800-2 and EN 61800-5-1	
Shock resistance	Shock test with severity level 1 to FN 942017-5 and EN 61800-2	
Maintenance interval	Lifetime lubrication	

Data sheet

**Materials**

Sectional view




Rotary drive		
[1]	Housing	Anodised wrought aluminium alloy
[2]	Clamping ring	Anodised wrought aluminium alloy
[3]	Rotating plate	Anodised wrought aluminium alloy
[4]	Ball bearing	Rolled steel
	Sealing ring	NBR
	Note on materials	RoHS-compliant
		Contains paint-wetting impairment substances

**Pin allocation**

Power supply

Plug

M12x1, 4-pin, T-coded to EN 61076-2-111




Pin	Function
1	Power voltage supply (24 V DC)
2	Reference potential, power voltage supply (GND)
3	Reserved, do not connect
4	Functional earth (FE)

Logic interface

Plug

M12x1, 8-pin, A-coded to EN 61076-2-101



When used with digital I/O	
Pin	Function
1	Logic voltage supply (24 V DC)
2	Digital output 1 (State "In")
3	Digital output 2 (State "Out")
4	Reference potential, logic voltage supply (GND)
5	Digital input 1 (Move "In")
6	Digital input 2 (Move "Out")
7	Reserved, do not connect
8	Reference potential, logic voltage supply (GND)

When used with IO-Link	
Pin	Function
1	L+ IO-Link power supply (24 V DC)
2	Reserved, do not connect
3	C/Q communication with the IO-Link master
4	L – Reference potential, IO-Link power supply (0 V)
5	Reserved, do not connect
6	Reserved, do not connect
7	Reserved, do not connect
8	L – Reference potential, IO-Link power supply (0 V)

## Data sheet

### Sizing example

Application data:

- Mass moment of inertia: 100 kgcm<sup>2</sup>
- Mounting position: horizontal
- Rotation angle: 180°
- Max. permitted positioning time: 1 s (one direction)


Step 1: Selection of the possible size from the table → page 8

#### Mechanical data

Size	25	32
Permissible mass moment of inertia [kgcm <sup>2</sup> ]	65	164


→ Smallest possible size: ERMS-32-180

Step 2: Selection of max. velocity level v for mass moment of inertia



→ Max. speed level for payload: level 10

Step 3: Reading off the min. positioning time t for rotation angle



— 90°  
- - - 180°

→ Min. positioning time for 180° at level 10: 0.5 s


### Result

The application can be implemented using ERMS-32-180. A minimum positioning time (one direction) of 0.5 s is achieved. Longer positioning times can be selected at any time using a lower speed level.


Data sheet

Mass moment of inertia  $m$  as a function of velocity level  $v$

Size 25




Size 32




Positioning time  $t$  as a function of velocity level  $v$  and rotation angle

Size 25




Size 32



— 90°  
- - - 180°

— 90°  
- - - 180°

Torque  $M$  as a function of force level  $F1$





— ERMS-25  
- - - ERMS-32

Data sheet



Max. permissible axial and radial force  $F_x/F_z$

Size		25		32
<b>Static</b>				
Axial force $F_x$	[N]	700		800
Radial force $F_z$	[N]	1200		2000
<b>Dynamic</b>				
Axial force $F_x$	[N]	350		450
Radial force $F_z$	[N]	450		550

Max. dynamic axial force  $F_x$  as a function of lever arm  $l$



Max. dynamic radial force  $F_z$  as a function of lever arm  $l$




## Data sheet

### Axial eccentricity and concentricity


#### Axial eccentricity

Measured on the surface of the rotating plate at the plate edge, when new.



#### Concentricity

Measured at the centring hole of the rotating plate, when new.




Size		25	32
Axial eccentricity Y	[mm]	<0.02	<0.04
Concentricity Z	[mm]	<0.02	<0.04


Data sheet

Dimensions

Download CAD data → [www.festo.com](http://www.festo.com)



View A



- [1] Connection to logic interface
- [2] Connection for power supply



## Data sheet

Size	B1 ±0.3	B2	B3	B4 ±0.03	B5 ±0.02	B6 ±0.02	B7	D1 ∅	D2 ∅ H8	D3 ∅ f8	D4 ∅ ±0.02
25	83	65	44	40	40	25	101.6	10	15	76	30
32	105	85	58	60	–	25	120	16	20	96	42


Size	D5 ∅ H7	D6	D7	D8 ∅ H7	D9	D10 ∅	D11 ∅ ±0.5	D12 ∅	D13 ∅	D14 ∅ H7	D15
25	9	M6	M6	7	M5	50	106	10	5.5	7	M5
32	12	M8	M8	7	M5	65	135	11	6.6	–	–

Size	D16 ∅ H7	D17	D18 max.	D19	D32 ±0.02	H1	H2	H3 ±0.3	H4	H5 ±0.03
25	7	M5	10	M8x1	–	127.1	115.9	83	65	40
32	7	M5	9	M8x1	30	149	137.8	105	85	60

Size	H6	H7 ±0.02	H8	L1 ±1.5	L3 ±0.6	L4	L5 ±0.2	L6 ±0.1	L7 ±0.1	T1
25	32.5	25	10.5	129.8	51.3	39.3	10	10	4	9.5
32	–	25	15	127	46.5	34.5	12	10	6	15

Size	T2 +0.1	T3	T4 +0.1	T5	T6 +0.1	T7	T8	T9
25	2	16	1.5	8.5	2.5	5.5	1.5	1.5
32	2.5	20	1.5	10	2.8	6.8	–	1.5


## Ordering data

Ordering data	Size	Rotation angle	Part no.	Type
	25	90°	<b>8087819</b>	<b>ERMS-25-90-ST-M-H1-PLK-AA</b>
		180	<b>8087820</b>	<b>ERMS-25-180-ST-M-H1-PLK-AA</b>
	32	90°	<b>8087821</b>	<b>ERMS-32-90-ST-M-H1-PLK-AA</b>
		180°	<b>8087822</b>	<b>ERMS-32-180-ST-M-H1-PLK-AA</b>



## Ordering data – Modular product system





Ordering table					
Size	25	32	Conditions	Code	Enter code
Module no.	8087808	8087809			
Series	ERMS			<b>ERMS</b>	ERMS
Size	25	32		-...	
Nominal swivel angle [°]	90, 180	90, 180		-...	
Motor type	Stepper motor ST			<b>-ST</b>	-ST
Controller	Integrated			<b>-M</b>	-M
Control panel	Integrated			<b>-H1</b>	-H1
Bus protocol/actuation	NPN and IO-Link			<b>-NLK</b>	
	PNP and IO-Link			<b>-PLK</b>	
End-position detection	With integrated end-position sensing			<b>-AA</b>	-AA
Cable outlet direction	Standard				
	Left			<b>-L</b>	
	Right			<b>-R</b>	
Electrical accessories	Without				
	Adapter for operation as IO device			<b>+L1</b>	
Operating instructions	With operating instructions				
	Without operating instructions			<b>DN</b>	


Accessories


Ordering data – Centring sleeves				Data sheets → Internet: zbh	
	For size	Description	Part no.	Type	PU <sup>1)</sup>
	25	For centring the drive in the case of side mounting	<b>150927</b>	<b>ZBH-9</b>	10
	32		<b>189653</b>	<b>ZBH-12</b>	
	25, 32	For centring attachments on the rotating plate	<b>186717</b>	<b>ZBH-7</b>	
	25	For centring attachments in the middle of the rotating plate	<b>191409</b>	<b>ZBH-15</b>	
	32		<b>150901</b>	<b>SLZZ-25/16</b>	

1) Packaging unit

Ordering data – Supply cables				Data sheets → Internet: nebl	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part no.	Type
	Angled socket, M12x1, 4-pin	Cable, open end, 4-wire	2	<b>8080778</b>	<b>NEBL-T12W4-E-2-N-LE4</b>
			5	<b>8080779</b>	<b>NEBL-T12W4-E-5-N-LE4</b>
			10	<b>8080780</b>	<b>NEBL-T12W4-E-10-N-LE4</b>
			15	<b>8080781</b>	<b>NEBL-T12W4-E-15-N-LE4</b>
	Straight socket, M12x1, 4-pin	Cable, open end, 4-wire	2	<b>8080790</b>	<b>NEBL-T12G4-E-2-N-LE4</b>
			5	<b>8080791</b>	<b>NEBL-T12G4-E-5-N-LE4</b>
			10	<b>8080792</b>	<b>NEBL-T12G4-E-10-N-LE4</b>
			15	<b>8080793</b>	<b>NEBL-T12G4-E-15-N-LE4</b>


Ordering data – Connecting cables				Data sheets → Internet: nebc	
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part no.	Type
	Angled socket, M12x1, 8-pin	Cable, open end, 8-wire	2	<b>8094476</b>	<b>NEBC-M12W8-E-2-N-B-LE8</b>
			5	<b>8094478</b>	<b>NEBC-M12W8-E-5-N-B-LE8</b>
			10	<b>8094481</b>	<b>NEBC-M12W8-E-10-N-B-LE8</b>
			15	<b>8094479</b>	<b>NEBC-M12W8-E-15-N-B-LE8</b>
	Straight plug, M12x1, 8-pin	Cable, open end, 8-wire	2	<b>8080786</b>	<b>NEBC-M12W8-E-2-N-M12G8</b>
			5	<b>8080787</b>	<b>NEBC-M12W8-E-5-N-M12G8</b>
			10	<b>8080788</b>	<b>NEBC-M12W8-E-10-N-M12G8</b>
			15	<b>8080789</b>	<b>NEBC-M12W8-E-15-N-M12G8</b>
	Straight socket, M12x1, 8-pin	Cable, open end, 8-wire	2	<b>8094480</b>	<b>NEBC-M12G8-E-2-N-B-LE8</b>
			5	<b>8094477</b>	<b>NEBC-M12G8-E-5-N-B-LE8</b>
			10	<b>8094482</b>	<b>NEBC-M12G8-E-10-N-B-LE8</b>
			15	<b>8094475</b>	<b>NEBC-M12G8-E-15-N-B-LE8</b>
	Straight plug, M12x1, 8-pin	Cable, open end, 8-wire	2	<b>8080782</b>	<b>NEBC-M12G8-E-2-N-M12G8</b>
			5	<b>8080783</b>	<b>NEBC-M12G8-E-5-N-M12G8</b>
			10	<b>8080784</b>	<b>NEBC-M12G8-E-10-N-M12G8</b>
			15	<b>8080785</b>	<b>NEBC-M12G8-E-15-N-M12G8</b>

 **Note**  
The cables are positioned at a 45° angle to the axis.



## Accessories

Ordering data – IO-Link master USB					Data sheets → Internet: cdsu
	Description	Cable length [m]	Part no.	Type	
	<ul style="list-style-type: none"> <li>For using the unit with IO-Link</li> <li>An external power supply plug is additionally required (not included in the scope of delivery)</li> </ul>	0.3	<b>8091509</b>	<b>CDSU-1</b>	

Ordering data – Adapter					Data sheets → Internet: nefc
	Electrical connection, left	Electrical connection, right	Cable length [m]	Part no.	Type
	Straight socket, M12x1, 8-pin	Straight plug, M12x1, 5-pin	0.3	<b>8080777</b>	<b>NEFC-M12G8-0.3-M12G5-LK</b>