

## Shrink-fit chuck 4.5° HSK 63 „Volume Shrink“ with resealable coolant bores (= KKB)

**ATORN®**

### Application

For clamping cutters and drills with straight shanks in h6 tolerance. Suitable for heavy-duty machining.

### Version

- Guaranteed maximum concentricity 0.003 mm
- Shrink grip and shrink release of HM and HSS tools
- Hardness 52 + 2 HRC
- Maximum coolant pressure 80 bar
- Adjustment travel 10 mm, can be adjusted on both sides
- 4 additional holes for fine balancing
- Hole for Balluff chip
- Geometry significantly improves shock-absorption

### Advantage

- High transmittable torques
- High chip removal rate, perfect for HSC machining
- Protects spindle and machine
- Ideal for high rotation speeds
- Improved surface quality



<b>Art. no.</b>	<b>23424 743</b>
<b>Tool holding device</b>	HSK 63
<b>Clamping diameter</b>	12 mm
<b>Projecting length</b>	70 mm
<b>Outer diameter</b>	33.3 mm
<b>Tapered diameter</b>	26.5 mm
<b>Clamp in depth</b>	40 mm
<b>Suitable for thread</b>	M8 x 1
<b>Width across flats</b>	3 mm
<b>Max. adjustment travel</b>	3 mm
<b>Concentricity tolerance</b>	0.003 mm
<b>Coolant supply</b>	KKB
<b>Balancing quality</b>	G 2.5 at 25 rpm

### EAN-Code

4050293407846