

Contactless voltage tester

Model testo 745



Application:

With the testo 745 non-contact voltage tester, you can quickly and easily determine the voltage or absence of voltage.

Advantage:

- Filters for high-frequency interference signals, thus more reliable voltage indication
- Visual and audible warning signal when AC voltage is detected
- Adjustable sensitivity in two levels: Stage 1 for phase determination, stage 2 for voltage indication
- Built-in pocket torch for illuminating measuring points in darkness
- Waterproof and dustproof according to degree of protection IP 67

Delivery:

Non-contact voltage tester testo 745 including 2x AAA batteries, calibration log and operating instructions.



Art. no.	75018 200
Brand	TESTO
Manufacturer Part Number	0590 7450
Min./max. voltage range AC	12-1000 V/AC
Overvoltage protection category	CAT III / 1000 V, CAT IV / 600 V
EN standard	61326-1, 61010-1 (VDE 0411-1)
Phase sequence test	Yes
Gross Weight	110.000 g
Product Group	4CF

EAN

4029547013881