

# SERIES 1881 - SINGLE-POLE ROUND ROCKER SWITCHES

TO 12 (4) A 250 V AC



## PRODUCT FEATURES

- ◆ Attractive round rocker switch
- ◆ High mechanical rating with at least 100 000 switching cycles
- ◆ Variants with IP 51
- ◆ Low depth with 18.7 mm
- ◆ Appliance cut-out with 20 mm

## ON REQUEST
























- ◆ Other colors
- ◆ Other printing variants
- ◆ Other terminal variants (e.g. PCB)
- ◆ Cable assembly
- ◆ Gold-plated contacts for low voltages
- ◆ Other switching functions (e.g. 1888 - middle off)
- ◆ Painted variants
- ◆ PVC-protection cap

Mechanical life endurance	10E4
Operating force	3 N
Inrush current (capacitive)	70 A
Contact resistance (new condition)	< 100 mOhm (1 A 12 V DC)
Insulation resistance (new condition)	> 100 MOhm (500 V DC)
Proof tracking	250 PTI
Protection type	IP 40 and IP 51 (product-dependent)
Ambient temperature	terminal side -20 °C ... +100 °C actuating side -20 °C ... +55 °C
Flammability	UL 94 V-2 UL 94 V-0 (product-dependent)
Glow wire test temperature	850 °C
Material	actuator PA housing PA terminals silver plated
Plug force of the terminals	≤ 80 N
Approval marks	
Suitable for appliances of protection class II	



# SERIES 1881 - SINGLE-POLE ROUND ROCKER SWITCHES

TO 12 (4) A 250 V AC

 single-pole	Actuator color / printing	Housing color	Terminal type								Terminal description	Contact distance in mm	Contact material	Actuator	EN 60335 cap. 30 conform "G"	Miscellaneous	Stock version
			12 (4) A 250 V AC 1E4	10 (4) A 250 V AC 1E4	8 (8) A 250 V AC 5E4	6 (4) A 250 V AV 5E4	15 A 250 V AC 1 1/2 HP	15 A 125 V AC 3/4 HP	10 A 250 V AC 1/2 HP	10 A 125 V AC 1/3 HP							
<b>ON / OFF switch (SPST)</b>																	
1881.1103		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40		●
1881.1104		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40		●
1881.1105		White	●	●	●	●						4.8	≥ 3	Ag	IP 40		
1881.1106		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40	●	
1881.1108		Black	●	●	●	●						4.8	≥ 3	Ag	IP 51	●	with switching system cover
1881.1109		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40		
1881.1111		Black	●	●	●	●						4.8	≥ 3	Ag	IP 40		
1881.1112		White	●	●	●	●						1 mm longer 4.8	≥ 3	Ag	IP 51	●	with switching system cover
<b>Normally open contact (SPNO)</b>																	
1881.1209		Black	●	●	●	●						4.8	≥ 3	Ag	IP 51		with switching system cover opening terminal 1b closed
<b>Changeover switch (SPDT)</b>																	
1883.1105		Black	●	●			●	●				4.8	≥ 3	Ag	IP 40		
1883.1106		Black	●	●			●	●				4.8	≥ 3	Ag	IP 40	●	

ROCKER SWITCHES

PUSHBUTTON SWITCHES

TOGGLE SWITCHES

SLIDE SWITCHES

ROTARY SWITCHES

FOOT SWITCHES

FACT AND KEY SWITCHES

SNAP-ACTION SWITCHES

MICRO-SIGNAL SWITCHES


SENSORS

# SERIES 1881 - SINGLE-POLE ROUND ROCKER SWITCHES


T0 12 (4) A 250 V AC




Basic type 1881



Quick-connect terminal 4.8 x 0.8



Quick-connect terminal 4.8 x 0.8  
1 mm longer




X = wall thickness

X	Ø
0.75 ... 1.25	20.3
1.25 ... 2	20.8
2 ... 3	21.1



Protection cap  
on request



Transparent PVC-protection cap.  
Serves as dust and water protection of  
the actuation side.