

Workshop crane, hydraulic

Mobile

Application:

For lifting heavy loads if the crane can move below the load.

Execution:

- Robust design
- Safe oil hydraulics with industry-standard engine oil
- No free overhang in front of wheels
- Mobile
- Load hook guard
- Pressure relief valve
- Drain valve with dead man's switch
- 2 steering rollers, 2 runners

Advantage:

- Robust design
- Easy to move, 360° rotating steering wheels
- Crane boom adjustable in just a few simple steps



Art. no.	77140 040
Brand	MAZZOLA/LONGUS
Manufacturer Part Number	007209039
Min./max. load-carrying capacity	700-2000 kg
Min./max. throat depth	1470-1920 mm
Min./max. construction height	1960-3345 mm
Min./max. lift height with minimum throat depth	900-2800 mm
Min./max. lift height with maximum throat depth	650-3145 mm
Inner running gear width	985 mm
Outer running gear width	1200 mm
Running gear length	2000 mm
Underride height	240 mm
Colour	Flame red RAL 3000
Load-carrying capacity	2000 kg
Max. construction height	3345 mm
Gross Weight	183.000 kg
Product Group	770