



### Product Information

Product Category	COOLING
Unit Barcode	5016368058138
Outer Carton Barcode	
Commodity Code	8414510090
Country of Origin	CHINA
Primary Colour	SILVER
Finish	PAINTED STEEL
Primary Material	STAINLESS STEEL
Warranty	2
Self Assembly	YES
Perishable Item	NO
Hazardous Item	NO

### General Product Specification

Voltage	230
Frequency	50
Wattage	45
Rated Current	0.2
Fuse Rating	6
Plug Type	BS 1363
Cable Diameter	0.75
Cable Length	1.5
Class	CLASS I
Conformity Markings	CE+UKCA

### Packaging & Shipping Information

Product Dimensions H x W x D (mm)	1250	400	400
Packaged Dimensions H x W x D (mm)	580	165	465
Outer Carton Dimensions H x W x D (mm)	590	340	480
Outer Carton Qty.	2		
Unit Weight (Kg)	6.3		
Unit Packaged Weight (Kg)	6.5		
Carton Weight (Kg)	13.5		
EPS (Kg)	PPT Exempt Plastic (Kg)		
Other Plastic (Kg)	0.024	Card / Paper (Kg)	0.3
Aluminium (Kg)	Steel (Kg)		

### Category Specific Technical Information

Fan Type	PEDESTAL	Tilt	YES
Number of Speed Settings	3	Maximum Tilt Angle	25
Number of Fan Modes		Oscillation	YES
Timer	NO	Maximum Oscillation Angle	65
Timer Length		Air Flow Rate	65.9
Remote Control	NO	Rotations per Minute at Highest Speed Setting	1350
Control Type	BUTTON	Rotations per Minute at Lowest Speed Setting	1100
Digital Display	NO	Tip Over Switch	NO
Ambient Room Temperature Display	NO	Auto Shutoff	NO
Number of Blades	4	Power Indicator Light	NO