



SIMBOX XL - HOLLOW WALL 2 ROWS - 2 X 12 MW
(14 MW) SAFETY CLASS II

Model		
product brand name		SIVACON
Design of the cap/top cover		closed
Design of the product / EMC version		No
Protection class		
Protection class IP		IP30
Operating resource protection class		2
Electricity		
Current / with AC / Rated value / maximum	A	63
Main circuit		
Operating voltage / with AC / Rated value	V	400
Appearance		
Color		white
Product details		
Product component		
• DIN mounting panel		Yes
• Mounting plate		No
• transparent cover		No
Product expansion / optional / Side-by-side mounting		No
Number		
Number of rows		2
Mechanical Design		

Height	mm	525
Width	mm	365
Depth	mm	102
Installation depth	mm	70
Number of width units		12
Mounting type		hollow wall
Opening angle of door	°	125
Busbar center-to-center spacing	mm	125
Material / of the enclosure		plastic

Certificates

Equipment marking

- acc. to DIN EN 61346-2
- acc. to DIN EN 81346-2

A

A

General Product Approval

Declaration of Conformity



Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/lowvoltage/catalogs>

Industry Mall (Online ordering system)

<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/8GB50244KM>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/8GB50244KM/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)


http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=8GB50244KM

CAX-Online-Generator


<http://www.siemens.com/cax>

Tender specifications

<http://ausschreibungstexte.siemens.com/tiplv>



last modified:



11.03.2015