


1204 EKTN9


Dimensions



d	20	mm
D	47	mm
B	14	mm
d_1	≈ 28.88	mm
D_1	≈ 40	mm
$r_{1,2}$	min. 1	mm

Tapered bore, taper 1:12

Abutment dimensions



D_a	max. 41.4	mm
r_a	max. 1	mm

Calculation data

Basic dynamic load rating	C	12.7	kN
Basic static load rating	C_0	3.4	kN
Fatigue load limit	P_u	0.18	kN
Reference speed		32000	r/min
Limiting speed		20000	r/min
Permissible angular misalignment	α	2.5	°
Calculation factor	k_r	0.04	
Calculation factor	e	0.3	
Calculation factor	Y_0	2.2	
Calculation factor	Y_1	2.1	
Calculation factor	Y_2	3.3	

Mass

Mass bearing	0.12	kg
--------------	------	----

