

Line laser, green, 532 nm, 90 °, 10 mW

LH532-10-24(20x80)-M12
Order Number: 70133721

Main Parameters (*)	min	typ	max	Unit
Wavelength		532		nm
Optical Output Power		10		mW
Operating Voltage	21.6	24	26.4	V DC
Operating Current	100	150	250	mA
Operating Temperature	15		30	°C
Storage Temperature	-40		80	°C

Main Data

Warranty	1 years
----------	---------

Technical Parameters

Lifetime	> 6,000 h
RoHS	yes

Optical Parameters

Beam Shape	Line
Laser Class	2M
Divergence	H - 1.0 mrad
Fan Angle	90 °
Line Thickness	<1.5mm@3m
Operating Distance	2 m
Optics	glass lens AR coated
Beam Mode	TEM00
Laser technology	Solid State (YVO4+KTP)
Stability	+/- 10% @ 15-30°C
Protection Lens	yes
Focus	fixed (3000mm)
Warm up time	< 15 min

Electrical Parameters

Potential of Housing	isolated
Connector	CON-M12

Mechanical Parameters

Size	Ø20x80 mm
Material	aluminium
Output Aperture	5.5 mm
Housing Color	black
Weight	80 g
Protection Class	IP 64


(*) Over the complete operating temperature range

Features




- Operating Voltage 24 V DC
- Isolated housing
- Laser Class 2M
- Protection lens
- M12 Connector

Picture



Safety Label



Valid Revision

| 11-FEB-2021