


REVISIONS

DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
1906	A	RELEASED	EO	04/17/06	TL	05/25/06	HO	05/25/06



J1	GROPE	COLOR	J2
1		RED	1
2	TROOP A(1)	WHITE	2
3		DRAIN	3
4		GREEN	4
5	TROOP A(2)	WHITE	5
3		DRAIN	3
6	TROOP B(8)	ORANGE	6
7		YELLOW	7
9		BROWN	9
10	TROOP A(3)	WHITE	10
11		DRAIN	11
12		BLUE	12
13	TROOP A(4)	WHITE	13
11		DRAIN	11

J1	GROPE	COLOR	J2
14	TROOP C(9)	VIOLET	14
15	TROOP C(10)	WHITE	15
16	TROOP C(11)	RED	16
17		GRAY	17
18	TROOP A(5)	BLACK	18
19		DRAIN	19
20		PINK	20
21	TROOP A(6)	ORANGE	21
19		DRAIN	19
22		DRAIN	22
23	TROOP A(7)	L/T GREEN	23
24		VIOLET	24
SHELL		BRAID	SHELL

NOTE:

- 1- CABLE: [28AWG(7/0.127)x1P+DRAIN(7/0.127)+AL/MY+MY]x7C+28AWG(7/0.127)x1P+28AWG(7/0.127)x3C+AL/MY+AL+85%(24/8/0.12)BRAID]TIN
INSULATION(A): Foam-PE, OD=ø0.95±0.05mm, UL-1598, COLOR: SEE WIRE LIST
INSULATION(B): HD-PE, OD=ø0.70±0.05mm, UL1598, COLOR: SEE WIRE LIST
INSULATION(C): HD-PE, OD=ø0.70±0.05mm, UL1598, COLOR: SEE WIRE LIST
JACKET: PVC, OD=ø8.6±0.15mm, UL20276, COLOR: BLACK
PRINT(FOR PI): "PAN-INTERNATIONAL 20276 E87647 9J AWM 80°C 30V VW-1"
- 2- 100% TEST OPEN, SHORT, MISWIRE
- 3- SPECIFICATION SAME AS DIGITAL VISUAL INTERFACE VER:1.0

DISCLAIMER:
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.

TOLERANCES:
UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:	DATE:
EKLAS ODISH	04/17/06
CHECKED BY:	DATE:
THOMAS LEE	05/25/06
APPROVED BY:	DATE:
HISHAM ODISH	05/25/06

DRAWING TITLE: DVI Cable, 10FT Dual Link, M/M, RoHS			
SIZE	DWG. NO.	ELECTRONIC FILE	REV
A	SPC19949	83K3692.DWG	A
SCALE: NTS	U.O.M.: Millimeters	SHEET: 1 OF 1	