

## SCSC clamping holder, positive, right

For longitudinal turning with CC indexable insert

**ATORN**<sup>®</sup>

### Application


For longitudinal turning with CC indexable insert, 80°

### Version

- precision-manufactured steel carrier, bronzed, hardened, type S, attack angle 45°, tip angle 90°, clearance angle 7°

### Advantage

- Robust geometry for longitudinal turning
- positive body geometry ensures low cutting forces



<b>Art. no.</b>	<b>17830 831</b>
<b>ISO name</b>	SCSC R/L 0808 D06
<b>Shaft height</b>	8 mm
<b>Shank width</b>	8 mm
<b>Length</b>	60 mm
<b>Length of head</b>	12 mm
<b>Programming size</b>	10 mm
<b>Suitable for indexable inserts</b>	CC.. 0602..
<b>Tool design</b>	Left

### EAN-Code

4050293562798

