

TE Type T - Immersion/penetration sensor

watertight, EN 13485 and HACCP-compliant



Application:

The waterproof standard immersion and penetration sensor is mainly suitable for measuring the core temperature of food.

Execution:

- Sensor type: TE Type K
- Measuring range: -50 to +350 °C
- Accuracy: $\pm 0.2^{\circ}\text{C}$ at -20 to +70 °C
- Accuracy: Class 1 (remaining measuring range)
- Response time: 7 s
- Length/diameter of probe/sensor tube: 115 mm/5 mm
- Length/diameter of probe/sensor tube tip: 50 mm/4 mm
- Product/housing material: ABS/TPE/PUR
- Degree of protection IP 65



Art. no.	46108 185
Brand	TESTO
Manufacturer Part Number	0603 1293
Sensor type	TE type T
Probe type	Immersion/insertion probe
Min./max. temperature measuring range	-50 to 350 °C
Accuracy temperature	+/- 0.2 °C at -20 to +70 °C, Class 1 (remaining measuring range)
Response time sensor	7 s
Diameter probe tube	5 mm
Diameter sensor tube tip	4 mm
Length sensor tube	115 mm
Length sensor tube tip	50 mm
Cable length	1.2 m
EN standard	60584-1
Material of housing	ABS/TPE/PUR
Gross Weight	0.150 kg
Product Group	4CF

EAN

4029547003837