

## KFMPB 15-10 F laminate trimmer

1550 W

metabo®

### Application:

Metal laminate trimmer for welding seam preparation

### Version:

- One-touch controller: patented tool-free milling depth adjustment in 0.1 mm increments; stop points for short adjustment times, which prevent accidental adjustment of cutting depth when working
- Universal milling head with three cemented carbide indexable inserts for all chamfer angles of 0-90°
- Stop roller for guidance on tubes for easy weld seam preparation
- Tool-free adjustable recessed handle for safe and even guiding

### Advantage:

- Patented mechanical braking system stops the cutter within 2 seconds after power off
- Precise setting of chamfer angle directly via the guide plates
- Side plates protect the user from chips

### Delivery:

3x cemented carbide universal reversible tips, stop roller, TX 15 screwdriver, SW 4 screwdriver with T-handle, SW 10 open-end spanner, additional handle, sheet steel carrying box



<b>Art. no.</b>	<b>71027 413</b>
<b>Max. idle speed</b>	12500 rpm
<b>Model</b>	KFMPB 15-10 F
<b>Manufacturer Article Number</b>	60 1755500
<b>Power input</b>	1550 W
<b>Power output</b>	840 W
<b>Max. chamfer height 45°</b>	10 mm
<b>Max. chamfer width 45°</b>	14 mm
<b>Weight</b>	5.1 kg
<b>Cable length</b>	4 m
<b>With soft start</b>	Yes
<b>With overload protection</b>	Yes
<b>With restart protection</b>	Yes
<b>With electronic feedback</b>	Yes
<b>With dead man function</b>	Yes

### EAN-Code

4007430298416