

Pneumatic straight grinder SRD 3-85/2

80 watt



Application:

For fine grinding, milling and engraving work.

Execution:

- Environmentally friendly owing to central air discharge
- Air discharge to the rear

Advantage:

- Very light and handy - extremely slim design.

Delivery:

Includes Collet chuck ZG 5/3 mm, collet chuck spanner 6 + 8 and hose unit; in box



Art. no.	75036 015
Brand	BIAX DRUCKLUFT
Manufacturer Part Number	150001060
Model	SRD 3-85/2
Valve design	Rotary valve
Max. idle speed	85000 rpm
Power output	80 W
Air consumption	170 l/min
Connection thread	M16
Inner hose diameter	4.5 mm
Length	173 mm
Diameter of housing	19.5 mm
Max. clamping diameter	3 mm
Collet chuck diameter	3 mm
Suitable for max. sanding block diameter	6 mm
Max. HM rotating milling cutter diameter	4 mm
Weight	0.13 kg
Gross Weight	0.892 kg
Product Group	748