

# TRMS FLEXIBLE CLAMP METER 3000A AC

## DCM4018FLEX



- "5 in 1" - ACA, ACV, DCV,  $\Omega$ , Hz functions
- TRMS
- AC current measurement up to 3000 A (limits 30A/ 300A/ 3000A)
- DC and DC voltage measurement up to 1000V
- Resistance measurement up to 10 k $\Omega$
- Frequency measurement up to 10 kHz
- Simultaneous display of 2 parameters: "voltage / frequency", "current / frequency",
- hold readings / SmartHOLD
- Ergonomic design with one-handed handle
- Auto power off
- low battery indication
- Bluetooth wireless interface (KPS Link)
- LCD display (4-digit "9999") with backlighting
- Drop test (1.3 m),
- Built-in torch
- Safety: IEC 61010-1, 600 V (cat IV), 1000 V (cat III)



# DCM4018FLEX

## TRMS FLEXIBLE CLAMP METER 3000A AC

| General                  |                             |
|--------------------------|-----------------------------|
| Display                  | 3000 counts                 |
| Auto power off           | ✓                           |
| Backlight                | ✓                           |
| Hold                     | ✓                           |
| Batteries                | AAA x2(R03, LR03, 24D, 24A) |
| Dimensions               | 57mm x 220mm x 35mm         |
| Weight                   | 200 g                       |
| Safety rating            | CAT IV 600V, CAT III 1000V  |
| Accessories included     | Standard test leads, punch  |
| Specs                    |                             |
| TRMS                     | ✓                           |
| AC /DC Voltage           | 1000V                       |
| AC current               | 0,01A - 3000 A              |
| Resistance               | 10k $\Omega$                |
| Frequency                | 10kHz                       |
| Jaw Length               | 45cm                        |
| Jaw section              | 7,5mm                       |
| Safety category          | CAT IV 600V, CAT III 1000V  |
| Product Code Information |                             |
| SKU                      | KPSDCM4018FLEXCBINT         |
| EAN code                 | 8435394787275               |
| UPC code                 | 810053677766                |
| Pcs/export carton        | 20                          |