



Part Number : [901361302](#)

Product Description : C-Grid III PC Board Connector, Dual Row, Vertical, 20 Circuits, Gold (Au) Plating

Series Number : 90151

Status : Active

Product Category : PCB Headers and Receptacles



Documents & Resources

Drawings

[Drawing 901512320_sd.pdf](#)

[Packaging Design Drawing PK-90151-001-001.pdf](#)

3D Models and Design Files

[3D Model 901512320_stp.zip](#)

Specifications

[Application Specification 713080001-AS-000.pdf](#)

[Application Specification 901190001-AS-000.pdf](#)

[Product Specification PS-99020-0001-001.pdf](#)

Product Environment Compliance

Compliance

GADSL/IMDS	Not Relevant
China RoHS	
EU ELV	Not Relevant
Low-Halogen Status	Not Low-Halogen per IEC 61249-2-21
REACH SVHC	Not Contained per D(2023)3788-DC (14 Jun 2023)
EU RoHS	Compliant per EU 2015/863

Multiple Part Product Compliance Statements

- Eu RoHS
- REACH SVHC
- Low-Halogen

Multiple Part Industry Compliance Documents

- IPC 1752A Class C
- IPC 1752A Class D
- Molex Product Compliance Declaration
- IEC-62474
- chemSHERPA (xml)

EU RoHS Certificate of Compliance

Part Details

General

Status	Active
Category	PCB Headers and Receptacles
Series	87760
Description	2.00mm Pitch Milli-Grid Header, Right-Angle, Through Hole, 38 Circuits, 0.38µm Gold (Au) Selective Plating, Tray, Lead-Free
Application	Board-to-Board, Signal, Wire-to-Board
Comments	Lead-Free version of 87049 series
Component Type	PCB Header
Product Family	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	822348273836

Agency

CSA	LR19980
UL	E29179

Electrical

Current - Maximum per Contact	2.0A
Voltage - Maximum	125V

Physical

Breakaway	No
Circuits (Loaded)	38
Circuits (maximum)	38

Color - Resin	Black
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	None
Mated Height	4.00mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	1.499/g
Number of Rows	2
Orientation	Right Angle
Packaging Type	Tray
PC Tail Length	2.60mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.381µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Polarized to PCB	No
Shrouded	No
Stackable	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface Style	Through Hole

Solder Process Data

Max-Duration	14
Lead-Free Process Capability	WAVE
Max-Cycle	1

Max-Temp	265
----------	-----

Mates With / Use With

Mates with Part(s)

Description	Part Number
Milli-Grid Vertical Through Hole PCB Receptacles	<u>78787</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>79107</u>
Milli-Grid Vertical Through Hole PCB Receptacles	<u>79108</u>
Milli-Grid Top Entry Surface Mount PCB Receptacles	<u>78788</u>
Milli-Grid Top/Bottom Entry Surface Mount PCB Receptacles	<u>79109</u>
Milli-Grid Top Entry Surface Mount PCB Receptacles	<u>87381</u>
Milli-Grid Side Entry Through Hole PCB Receptacles	<u>87264</u>